




TOP VIEW

| SYMBOLS | MIN. | NOM. | MAX. |
|---------|------------|------|------|
| A | 0.30 | 0.35 | 0.40 |
| A1 | 0.00 | 0.02 | 0.05 |
| A3 | 0.127 REF. | | |
| b | 0.15 | 0.20 | 0.25 |
| D | 1.95 | 2.00 | 2.05 |
| E | 1.95 | 2.00 | 2.05 |
| e | 0.40 BSC | | |
| L | 0.15 | 0.25 | 0.35 |
| D2 | 0.95 | 1.00 | 1.05 |
| E2 | 0.95 | 1.00 | 1.05 |



BOTTOM VIEW



RECOMMENDED LAND PATTERN

NOTE :

1. ALL DIMENSIONS ARE IN mm. ANGLES IN DEGREES.
2. REFER JEDEC MO-288
3. RECOMMENDED LAND PATTERN IS FOR REFERENCE ONLY. MESH STENCIL DESIGN IS RECOMMENDED.