




TOP VIEW



BOTTOM VIEW





SIDE VIEW



Recommend Land Pattern (Recommend Thermal Via)

PKG. DIMENSIONS(MM)			
SYMBOL	Min	NOM	Max
A	0.66	0.73	0.80
A2	0.24	0.28	0.32
A3	0.42	0.45	0.48
D	6.00	6.10	6.20
E	2.60	2.70	2.80
D1	5.00 TYP		
E1	0.70 TYP		
D2	5.00 TYP		
E2	0.70 TYP		
L	0.30 TYP		
b	0.17 TYP		
b1	0.20 TYP		
b2	0.20 TYP		
e	0.40 BSC		
e1	1.20 TYP		
S	0.30 REF		
S1	0.25 REF		
aaa	0.10		
bbb	0.10		
ddd	0.08		

Notes:  
1. ALL DIMENSIONS ARE IN mm.

 	<b>DATE: 11/30/23</b>
<b>DESCRIPTION: W-LGA6127-31</b>	
<b>PACKAGE CODE: FLA(FLA31)</b>	
<b>DOCUMENT CONTROL#: PD-2288</b>	<b>REVISION:--</b>