


NPN SILICON PLANAR MEDIUM POWER TRANSISTOR

2N6731

ISSUE 1 – MARCH 94

FEATURES

- * 80 Volt V_{CEO}
- * Gain of 100 at $I_C = 350$ mA
- * $P_{tot} = 1$ Watt



E-Line
TO92 Compatible

ABSOLUTE MAXIMUM RATINGS.

| PARAMETER | SYMBOL | VALUE | UNIT |
|---|----------------|-------------|------------------|
| Collector-Base Voltage | V_{CBO} | 100 | V |
| Collector-Emitter Voltage | V_{CEO} | 80 | V |
| Emitter-Base Voltage | V_{EBO} | 5 | V |
| Peak Pulse Current | I_{CM} | 2 | A |
| Continuous Collector Current | I_C | 1 | A |
| Power Dissipation at $T_{amb} = 25^\circ\text{C}$ | P_{tot} | 1 | W |
| Operating and Storage Temperature Range | $T_j; T_{stg}$ | -55 to +200 | $^\circ\text{C}$ |

ELECTRICAL CHARACTERISTICS (at $T_{amb} = 25^\circ\text{C}$ unless otherwise stated).

| PARAMETER | SYMBOL | MIN. | TYP. | MAX. | UNIT | CONDITIONS. |
|---------------------------------------|---------------|------------|------|------|---------------|---|
| Collector-Base Breakdown Voltage | $V_{(BR)CBO}$ | 100 | | | V | $I_C = 100\mu\text{A}$, $I_E = 0$ |
| Collector-Emitter Breakdown Voltage | $V_{(BR)CEO}$ | 80 | | | V | $I_C = 10\text{mA}$, $I_B = 0^*$ |
| Emitter-Base Breakdown Voltage | $V_{(BR)EBO}$ | 5 | | | V | $I_E = 1\text{mA}$, $I_C = 0$ |
| Collector Cut-Off Current | I_{CBO} | | | 0.1 | μA | $V_{CB} = 80\text{V}$, $I_E = 0$ |
| Emitter Cut-Off Current | I_{EBO} | | | 10 | μA | $V_{EB} = 5\text{V}$, $I_C = 0$ |
| Collector-Emitter Saturation Voltage | $V_{CE(sat)}$ | | | 0.35 | V | $I_C = 350\text{mA}$, $I_B = 35\text{mA}^*$ |
| Base-Emitter Turn-On Voltage | $V_{BE(on)}$ | | | 1.0 | V | $I_C = 350\text{mA}$, $V_{CE} = 2\text{V}^*$ |
| Static Forward Current Transfer Ratio | h_{FE} | 100 100 | | 300 | | $I_C = 10\text{mA}$, $V_{CE} = 2\text{V}^*$ $I_C = 350\text{mA}$, $V_{CE} = 2\text{V}^*$ |
| Transition Frequency | f_T | 50 | | 500 | MHz | $I_C = 200\text{mA}$, $V_{CE} = 5\text{V}$ $f = 20\text{MHz}$ |
| Collector-Base Capacitance | C_{CB} | | | 20 | pF | $V_{CB} = 10\text{V}$, $f = 1\text{MHz}$ |

*Measured under pulsed conditions. Pulse width=300 μs . Duty cycle $\leq 2\%$