



PKG. DIMENSIONS(MM)		
SYMBOL	Min	Max
A		0.625
A1	0.18	0.22
D	1.84	1.90
e	0.50 BSC	
E	1.34	1.40
b	0.24	0.28
ccc	0.05 TYP	
ddd	0.015 TYP	



Notes:

1. Ref:JEDEC MO-211C
2. RECOMMEND LAND PATTERN REFERENCE DIODES PKG U-WLB1520-12

		DATE: 01/19/22
DESCRIPTION: U-WLB1914-12, Wafer Level		
PACKAGE CODE: GA (GA12)		
DOCUMENT CONTROL#: PD-2156		REVISION: C