



TOP VIEW



BOTTOM VIEW





SIDE VIEW

| PKG. DIMENSIONS(MM) | | | |
|---------------------|-----------|-------|-------|
| SYMBOL | Min. | Nom. | Max. |
| A | 0.445 | 0.490 | 0.535 |
| A1 | 0.185 | 0.205 | 0.225 |
| A2 | 0.240 | 0.260 | 0.280 |
| A3 | 0.020 | 0.025 | 0.030 |
| D | 2.410 | 2.440 | 2.470 |
| E | 2.410 | 2.440 | 2.470 |
| D1 | 1.950 | 2.000 | 2.050 |
| E1 | 1.950 | 2.000 | 2.050 |
| b | 0.240 | 0.260 | 0.280 |
| X | 0.205 | -- | 0.235 |
| Y | 0.205 | -- | 0.235 |
| e | 0.400 BSC | | |
| SD | 0.200 BSC | | |
| SE | 0.200 BSC | | |

Note:

1. ALL DIMENSIONS ARE IN MILLIMETERS (ANGLES IN DEGREES).

| | |
|---|--|
|   | DATE: 02/01/19 |
| | DESCRIPTION: 36-Ball, WLCSP, 2.44x2.44 (U-WLB2424-36) |
| | PACKAGE CODE: GEA (GEA36) |
| | DOCUMENT CONTROL #: PD-2241 |
| | REVISION: A |