




TOP VIEW



SIDE VIEW




SIDE VIEW



DETAIL F

PKG. DIMENSIONS(MM)			
SYMBOLS	MIN.	NOM.	MAX.
A	—	—	1.20
A1	0.05	—	0.15
A2	0.80	1.00	1.05
b	0.19	—	0.30
c	0.09	—	0.20
D	2.90	3.00	3.10
E	6.20	6.40	6.60
e	0.65 BSC		
E1	4.30	4.40	4.50
L	0.45	0.60	0.75
L1	1.00 REF		
S	0.20	—	—
θ°	0	—	8



RECOMMENDED LAND PATTERN(unit:mm)

NOTES:

1. ALL DIMENSIONS IN MILLIMETERS. ANGLES IN DEGRESS.
2. JEDEC MO-153F/AA
3. DIMENSIONS DOES NOT INCLUDE MOLD FLASH, PROTRUSIONS OR GATE BURRS.
4. RECOMMENDED LAND PATTERN REFERENCE DIODES TSSOP8.



PERICOM A PRODUCT LINE OF DIODES INCORPORATED
ENABLING SERIAL CONNECTIVITY

DATE: 02/04/24

DESCRIPTION: 8-Pin, 173mil Wide TSSOP

PACKAGE CODE: L (L8)

DOCUMENT CONTROL#: PD-1308

REVISION: H