



PKG. DIMENSIONS(MM)		
SYMBOL	Min	Max
A	3.30	3.70
A1	1.10	1.40
b	0.38	0.55
c	0.36	0.51
D	4.30	4.70
D1	3.43	
E	4.30	4.70
e	1.27 TYP	
e1	2.44	2.64
L	14.10	14.50
phi		1.60
h	0.00	0.38

Note:



DATE: 06/18/13

DESCRIPTION: 3-Pin, T092

PACKAGE CODE: NB (NB3)

DOCUMENT CONTROL #: PD-2149

REVISION: --