




TOP VIEW



BOTTOM VIEW



SYMBOL	DIMENSION IN MM		
	MIN.	NOM	MAX.
A	0.89	0.97	1.05
A1	0.16	--	0.26
b	0.27	--	0.37
D	6.90	7.00	7.10
E	6.90	7.00	7.10
D1	6.00 BSC.		
E1	6.00 BSC.		
e	0.50 BSC.		



DESCRIPTION: 115-Ball, TFBGA 7X7mm (0.3mm Ball)

PACKAGE CODE: NK (NK115)

DOCUMENT CONTROL #: PD-2197

DATE: 07/23/15

REVISION: A

NOTE :  
 1. ALL DIMENSIONS ARE IN MILLIMETER. ANGLES IN DEGREE.  
 2. REFER JEDEC MO-195