



PKG. DIMENSIONS(MM)		
SYMBOL	Min	Max
A	3.71	4.31
A1	0.51	
A2	3.20	3.60
B	0.38	0.57
B1	1.52 BSC	
c	0.20	0.36
D	18.80	19.20
E	6.20	6.60
E1	7.32	7.92
e	2.54 BSC	
L	3.00	3.60
E2	8.40	9.00

Notes:

1. Refer JEDEC MS-001D/BB



DATE: 06/14/13

DESCRIPTION: 16-Pin, Dual InLine Plastic, DIP

PACKAGE CODE: P (P16)

DOCUMENT CONTROL #:PD-2136

REVISION: --