



PKG. DIMENSIONS(MM)		
SYMBOL	Min	Max
A	3.71	4.31
A1	0.51	
A2	3.20	3.60
B	0.38	0.57
B1	1.52 BSC	
c	0.20	0.36
D	25.95	26.55
E	6.20	6.60
E1	7.32	7.92
e	2.54 BSC	
L	3.00	3.60
E2	8.40	9.00

**Notes:**

1. Refer JEDEC MS-001D/BE



DATE: 11/11/14

DESCRIPTION: 22-Pin, Dual InLine Plastic, DIP

PACKAGE CODE: P (P22)

DOCUMENT CONTROL #:PD-2191

REVISION: -