



SYMBOLS	MIN.	NOM.	MAX.
A	—	—	0.069
A1	0.004	—	0.0098
A2	0.049	—	—
b	0.008	—	0.012
c	0.004	—	0.010
D	0.386	0.390	0.394
E1	0.150	0.154	0.158
E	0.228	0.236	0.244
L	0.016	—	0.050
L1	0.041 REF		
e	0.025 BSC		
θ°	0	—	8

UNIT : INCH



- NOTES:
1. ALL DIMENSIONS IN INCH. ANGLES IN DEGREES.
 2. JEDEC MO-137E
 3. DIMENSIONS DOES NOT INCLUDE MOLD FLASH, PROTRUSIONS OR GATE BURRS.



DATE: 03/30/16

DESCRIPTION: 28-Pin, 150mil Wide QSOP

PACKAGE CODE: Q (Q28)

DOCUMENT CONTROL #: PD-1204

REVISION: G