



PKG DIMENSIONS(MM)		
SYMBOL	Min.	Max.
A	--	1.10
A1	0.00	0.15
A2	0.75	0.95
b	0.17	0.33
c	0.08	0.23
D	2.80	3.20
E	4.65	5.15
E1	2.80	3.20
e	0.50 BSC	
L	0.40	0.80
L1	0.95 REF	
$\theta$	0°	8°

**NOTE:**

1. ALL DIMENSIONS ARE IN MILLIMETERS. ANGLES IN DEGREES.
2. REFER JEDEC MO-187F/BA
3. PACKAGE OUTLINE DIMENSIONS DO NOT INCLUDE MOLD FLASH AND METAL BURR.



DATE: 04/19/16

DESCRIPTION: 10-Pin, Mini Small Outline Package, MSOP

PACKAGE CODE: U (U10)

DOCUMENT CONTROL #: PD-1262

REVISION: F