



SYMBOLS	MIN.	NOM.	MAX.
A	—	—	1.20
A1	0.05	—	0.15
A2	0.80	1.00	1.05
b	0.19	—	0.30
C	0.09	—	0.20
D	6.40	6.50	6.60
E1	4.30	4.40	4.50
E	6.20	6.40	6.60
e	0.65 BSC		
L1	1.00 REF		
L	0.45	0.60	0.75
S	0.20	—	—
$\theta$	0°	—	8°



- NOTES:
1. ALL DIMENSIONS IN MILLIMETERS. ANGLES IN DEGREES.
  2. JEDEC MO-153F
  3. DIMENSIONS DOES NOT INCLUDE MOLD FLASH, PROTRUSIONS OR GATE BURRS.

	DATE: 03/31/16
	DESCRIPTION: 20-Pin, 173mil Wide TSSOP
	PACKAGE CODE: L (L20)
	DOCUMENT CONTROL #: PD-1311
	REVISION: G