



SYMBOLS	MIN.	NOM.	MAX.
A	—	—	1.20
A1	0.05	—	0.15
A2	0.80	1.00	1.05
b	0.17	—	0.27
c	0.09	—	0.20
D	13.90	14.00	14.10
E1	6.00	6.10	6.20
E	7.90	8.10	8.30
e	0.50 BSC		
L1	1.00 REF		
L	0.45	0.60	0.75
S	0.20	—	—
$\theta$	0°	—	8°



DETAIL F

	DATE: 03/30/16
	DESCRIPTION: 56-Pin, 240mil Wide TSSOP
	PACKAGE CODE: A (A56)
DOCUMENT CONTROL #: PD-1502	REVISION: N

- Notes:
1. Controlling Dimension in Millimeters. Angle in Degrees.
  2. Refer JEDEC MO-153F
  3. Package Outline Exclusive of Mold Flash and Metal Burr.