




TOP VIEW



BOTTOM VIEW



RECOMMENDED LAND PATTERN(mm)



SIDE VIEW

| PKG. DIMENSIONS(MM) | | | |
|---------------------|----------|------|------|
| SYMBOL | Min | TYP | Max |
| A | 0.45 | 0.50 | 0.55 |
| A1 | 0.00 | 0.02 | 0.05 |
| A3 | 0.15 REF | | |
| D | 2.95 | 3.00 | 3.05 |
| E | 3.95 | 4.00 | 4.05 |
| D1 | 1.60 | 1.65 | 1.70 |
| E1 | 2.60 | 2.65 | 2.70 |
| b | 0.15 | 0.20 | 0.25 |
| e | 0.50 BSC | | |
| L | 0.35 | 0.40 | 0.45 |

Note:
1. Ref: JEDEC MO-288B



DATE: 07/05/16

DESCRIPTION: 20-Pin, UQFN,3x4

PACKAGE CODE: XW (XW20)

DOCUMENT CONTROL #: PD-2129

REVISION: A