



PKG. DIMENSIONS(MM)			
SYMBOL	Min	NOM	Max
A	0.75	0.80	0.85
A1	0.00	0.02	0.05
A3	0.15 REF		
D	3.95	4.00	4.05
E	3.95	4.00	4.05
D1	2.60	2.70	2.80
E1	2.60	2.70	2.80
b	0.19	0.24	0.29
L	0.35	0.40	0.45
e	0.50 BSC		

**Notes:**

1. Comply with JEDEC MO-220K, except 'A'



DATE: 11/23/16

DESCRIPTION: 24-Pin, TQFN, 4X4mm

PACKAGE CODE: ZDA(ZDA24)

DOCUMENT CONTROL#: PD-2217

REVISION:--