




TOP VIEW



BOTTOM VIEW



RECOMMENDED LAND PATTERN(unit:mm)



SIDE VIEW

PKG. DIMENSIONS(MM)			
SYMBOL	Min	NOM	Max
A	0.75	0.80	0.85
A1	0.00	0.02	0.05
A3	0.15 REF		
D	3.45	3.50	3.55
E	3.45	3.50	3.55
D1	1.90	2.00	2.10
E1	1.90	2.00	2.10
b	0.20	0.25	0.30
e	0.50 BSC		
e1	1.50 BSC		
L	0.35	0.40	0.45

Note:

1. Comly with JEDEC MO-220K, except 'A', 'A3', 'D1' and 'E1'.



DATE: 02/15/17

DESCRIPTION: 14-Pin, TQFN, 3.5x3.5

PACKAGE CODE: ZDB (ZDB14)

DOCUMENT CONTROL #: PD-2222

REVISION: --