



PKG. DIMENSIONS(MM)		
SYMBOL	Min	Max
A	0.40	0.48
A1	0.08	0.12
D	1.66	1.72
E	1.76	1.82
b	0.13	0.17
e	0.40 BSC	
e1	0.35 BSC	
ccc	0.05 TYP	
ddd	0.015 TYP	

Notes:
1. NO JEDEC SPEC APPLIES

 	DATE: 05/09/17
	DESCRIPTION: 20-Pin,CSP,1.69X1.79,Wafer Level
PACKAGE CODE: GF(GF20)	
DOCUMENT CONTROL#: PD-2227	REVISION: --