



	SYMBOL	MIN	NOM	MAX
TOTAL THICKNESS	A	--	--	0.85
STAND OFF	A1	0.02	0.05	0.08
MOLD THICKNESS	A2	0.675 REF		
L/F THICKNESS	A3	0.127 REF		
LEAD WIDTH	b	0.15	0.20	0.25
	b1	0.15	0.20	0.25
BODY SIZE	X	D	9.90	10.00
	Y	E	9.90	10.00
LEAD PITCH	e	0.50 BSC		
	e1	4.175 BSC		
	e2	0.55 BSC		
	e3	3.30 BSC		
EP SIZE	X	J	5.90	6.00
	Y	K	5.90	6.00
LEAD LENGTH	L	0.30	0.35	0.40
	L1	5.95	6.00	6.05
PACKAGE EDGE TOLERANCE	aaa	0.10		
MOLD FLATNESS	bbb	0.20		
COPLANARITY	ccc	0.10		
LEAD OFFSET	ddd	0.08		
EXPOSED PAD TOLERANCE	eee	0.10		



NOTES  
 1.0 DIMENSIONS IN MILLIMETERS. ANGLES IN DEGREES.  
 2.0 COPLANARITY APPLIES TO LEADS, CORNER LEADS, RINGS AND DIE ATTACH PAD AS WELL AS THE TERMINALS.

DATE: 12/02/13

**PERICOM**  
Enabling Serial Connectivity

**DESCRIPTION: 136-contact, Advanced Quad Flat No-Lead (aQFN)**

**PACKAGE CODE: ZXA (ZXA136)**

**DOCUMENT CONTROL #: PD-2177**

**REVISION: --**