


**Package Outline Dimensions**

PDIP-8 (Type A1)



PDIP-8 (Type A1)						
Dim	Inches			Millimeters		
	Min	Max	Typ	Min	Max	Typ
<b>A</b>	--	0.210	--	--	5.334	--
<b>A1</b>	0.015	--	--	0.381	--	--
<b>A2</b>	0.125	0.135	0.130	3.175	3.429	3.302
<b>b</b>	--	--	0.018	--	--	0.457
<b>b2</b>	--	--	0.060	--	--	1.524
<b>c</b>	0.008	0.014	0.010	0.203	0.356	0.254
<b>D</b>	0.355	0.400	0.365	9.017	10.160	9.271
<b>E</b>	0.300 BSC			7.62 BSC		
<b>E1</b>	0.245	0.255	0.250	6.223	6.477	6.350
<b>eB</b>	0.335	0.375	0.355	8.509	9.525	9.017
<b>e</b>	--	--	0.100	--	--	2.540
<b>L</b>	0.115	0.150	0.130	2.921	3.810	3.302
<b>a</b>	0°	15°	7°	0°	15°	7°
<b>Controlling dimensions are in inches</b>						