




TOP VIEW



BOTTOM VIEW



RECOMMENDED LAND PATTERN (unit:mm)




SIDE VIEW

PKG. DIMENSIONS(MM)		
SYMBOL	Min	Max
A	-	1.10
A1	0.00	0.10
A2	0.70	1.00
b	0.15	0.40
c	0.08	0.22
D	1.80	2.20
E	1.10	1.40
E1	1.80	2.45
e	0.65 BSC	
L	0.26	0.46
θ	0°	8°

Notes:

1. Comply with MO-203C/AB, except b Max, D Min and D Max.
2. PACKAGE OUTLINE DIMENSIONS DO NOT INCLUDE MOLD FLASH AND METAL BURR
3. LAND PATTERN REFERENCE DIODES SOT363 PACKAGE INFORMATION.

	DATE: 12/16/21
	DESCRIPTION: 6-Pin, SOT363 (SC70)
PACKAGE CODE: C (C6)	
DOCUMENT CONTROL#: PD-1902	REVISION:D