


**Package Outline Dimensions**

**TO247-2 (Type WX)**



TO247-2 (Type WX)			
Dim	Min	Max	Typ
A	4.87	5.13	5.00
A1	2.10	2.40	2.38
A2	1.88	2.08	1.98
b	1.12	1.22	1.20
b1	1.90	2.16	2.00
b3	1.93	2.18	2.05
c	0.51	0.76	0.60
D	21.25	21.75	21.50
D1	--	--	16.93
D2	--	--	1.60
E	15.75	16.25	16.00
E1	--	--	14.02
E2	--	--	13.30
e	10.60	11.10	10.88
L	19.60	20.10	19.85
L1	3.78	4.38	4.08
L2	--	--	4.40
ØP	2.90	3.20	3.10
θ	--	--	20°
All Dimensions in mm			