


**Package Outline Dimensions**

TO247-2L (Type HE)



TO247-2L (Type HE)			
Dim	Min	Max	Typ
A	4.90	5.10	5.00
A1	2.31	2.51	2.41
A2	1.90	2.10	2.00
b	1.16	1.26	1.21
b2	1.91	2.21	2.01
c	0.59	0.66	0.61
D	20.90	21.10	21.00
D1	16.25	16.85	16.55
D2	1.05	1.35	1.20
E	15.70	15.90	15.80
E1	13.10	13.50	13.30
E2	4.90	5.10	5.00
E3	2.40	2.60	2.50
e	10.88 BSC		
h	0.05	0.15	0.10
L	19.80	20.10	19.92
L1	--	--	4.30
ØP	3.50	3.70	3.60
ØP1	--	--	7.30
ØP2	2.40	2.60	2.50
Q	5.60	6.00	5.80
S	6.15 BSC		
R	0.50 REF		
T	9.80	10.20	--
T1	1.65 REF		
T2	8.00 REF		
T3	12.80 REF		
U	6.00	6.40	--
Ø1	6°	8°	7°
Ø2	1°	6°	5°
Ø3	1°	1.5°	--
Ø4	14°	16°	15°
<b>All Dimensions in mm</b>			