


**Package Outline Dimensions**

TO247 (Type HE)



TO247 (Type HE)			
Dim	Min	Max	Typ
A	4.80	5.20	5.00
A1	2.21	2.59	2.41
A2	1.85	2.15	2.00
b	1.11	1.36	1.21
b1	2.91	3.21	3.01
b2	1.91	2.21	2.01
c	0.51	0.75	0.61
D	20.80	21.30	21.00
D1	4.80	5.20	5.00
D2	16.25	16.85	16.55
E	15.50	16.10	15.80
E1	2.30	2.70	2.50
E2	13.00	13.60	13.30
e	5.44 BSC		
L	19.82	20.22	19.92
L1	--	--	4.30
Q	6.15 BSC		
ØP	3.40	3.80	3.60
ØP1	--	--	7.30
All Dimensions in mm			