


Package Outline Dimensions

TO247 (Type WH)



TO247 (Type WH)			
Dim	Min	Max	Typ
A	4.83	5.21	--
A1	2.29	2.54	--
A2	1.91	2.16	--
b	1.07	1.33	--
b1	1.91	2.41	--
b3	2.87	3.38	--
c	0.55	0.68	--
D	20.80	21.10	--
D1	16.25	17.65	--
D2	0.95	1.25	--
E	15.75	16.13	--
E1	12.38	13.43	--
E2	3.68	5.10	--
E3	1.00	1.90	--
E4	13.10	14.15	--
e	5.44 BSC		
L	19.81	20.32	--
L1	4.10	4.40	--
Q	5.49	6.00	--
S	6.04	6.30	--
T	17.5° REF		
W	3.5° REF		
X	4° REF		
All Dimensions in mm			