



TOP VIEW




BOTTOM VIEW

PKG. DIMENSIONS(MM)		
SYMBOL	Min	Max
A	0.80	0.90
A1	0.00	0.05
A3	0.20 REF	
D	3.42	3.58
E	3.42	3.58
D1	1.95	2.15
E1	1.95	2.15
b	0.20	0.30
e	0.50 TYP	
e1	1.50 TYP	
L	0.32	0.48




SIDE VIEW



RECOMMENDED LAND PATTERN(unit:mm)

Notes:

- Controlling dimensions in millimeters.
- Ref: JEDEC MO-220
- LAND PATTERN REFERENCE DIODES V-DFN3535-14 PACKAGE INFORMATION

		DATE: 03/11/21
DESCRIPTION: 14-Pin, TQFN, 3.5*3.5		
PACKAGE CODE: ZB (ZB14)		
DOCUMENT CONTROL#: PD-2154		REVISION: A