









SIZE	QTY	SYM	PLATED	TOL
10	1282	✕	YES	+/-0.0
37	72	◇	YES	+/-0.0
50	6	⊠	YES	+/-0.0
29.53	22	⊕ <sup>F</sup>	YES	+/-0.0
28 x 88.58	16	⊕ <sup>G</sup>	YES	+/-0.0
28 x 64.96	16	⊕ <sup>H</sup>	YES	+/-0.0
33.46 x 78.74	18	⊕ <sup>I</sup>	YES	+/-0.0
39.37	24	⊕ <sup>J</sup>	YES	+/-0.0
93.7	12	⊕ <sup>K</sup>	YES	+/-0.0
20	20	⊕ <sup>L</sup>	YES	+/-0.0
43	5	⊕ <sup>M</sup>	YES	+/-0.0
137.8	16	⊕ <sup>N</sup>	YES	+/-0.0
12	8	⊕ <sup>O</sup>	YES	+/-0.0











