




PI6C4911504-01LIE_LVPECL Buffer_EVB


REV.A

Date:2015.7.7

S/N:



REF_IN0+
REF_IN0-
REF_IN1+
REF_IN1-




GND

EC1

VDD

VCC




IN_SEL

SYNC_OE

GND

VDD




Q0+


Q0-

2 inch

R1



Q0- 2 inch



GND


Q1+

Q1-

GND

R4

2 inch



GND


Q2+

Q2-

GND

R10

2 inch




GND

Q3-

Q3+

GND

R13



U1

C16

R18

R19

R20

R21

C17

R17

R16

R15

C18

R14

C15

R12

C13

R7

C12

R11

C11

R3


C4

R6

C11

R15

C18



SD

CS



PI6C4911504-01LIE_LVPECL Buffer_EVB

REV.A

Date:2015.7.7

S/N:

