


- \*Note 1: Suggest RX1/2 signals are reserved AC coupling to support non-compliant Type-C device. RX1/2 AC cap C7, C8, C3, C4 should be replaced by 0ohm resistors when DCI test.
- \*Note 2: Recommended AC coupling cap characters: 0201 or 0402, X5R/X7R.
- \*Note 3: Suggest to 0.22uF AC coupling cap to ensure risk free in USB-IF Compliance.
- \*Note 4: Reserve 200kohm to support non-compliant Type-C device.
- \*Note 5: Suggest MUX\_EN to be controlled by GPIO.

Revision	Description of the Change
1.0	1. Initial release
2.0	1. Change the Type-C side out AC coupling capacitors from 0.1uF to 0.22uF. 2. Add notes of the EN and AC coupling capacitors. 3. Add AC cap 0.1uF on AUXP/AUXN. 4. Add pull down resistance R11/12/13/14 200kohm on RX1/2 Type-C side for bias voltage.
2.1	1. Update mistake of 0.22F to 0.1uF of C22.
2.2	1. Update mistake of U2/U3 net name from CON_RX2+/RX2- to RX2+/RX2-_C, CON_RX1+/RX1- to RX1+/RX1-_C .

 <b>Pericom Semiconductor Corporation</b> <small>Enabling Serial Connectivity</small>	
Size A	Document Name <b>PI3DPX1205A App Source Rev Histtoy</b>
Date:	Sunday, January 22, 2017
Sheet	2 of 3
Rev	<b>2.2</b>