

Design tools

Crystal/Oscillator Search Tool, Sales Support & Sample Request



- Customizable crystal and XO characteristics
- IBIS and 3D STEP models
- Fast sample support
- Evaluation boards upon request
- Schematics and layout review
- Crystal matching service
- PCB debug support

Commercial value


- Cost-effective solutions
- Short lead times; expedited delivery upon request

Applications

- ADAS / LIDAR
- Telematics (T-Box)
- Electronic Control Units
- Infotainment
- Automotive exterior lighting

Automotive-compliant Frequency Control Products (FCP) & Clocks

Crystals + Oscillators + ICs from a single vendor optimized performance, cost, and ease of design



Clock Buffer IC

- Additive jitter as low as 10fs
- 1, 2, 4 outputs
- LVCMOS, LVDS outputs



PCIe Clock Gen and Clock Buffer IC

- PCIe 6.0/ 5.0/ 4.0/ 3.0 support
- Generators: 2, 4, 6, 8 outputs
- Buffers: 4 outputs



Real-Time Clock IC

- AEC-Q100 Grade 1, -40° to 125°C
- Full-featured, single/dual supply, I²C Interface



Crystals and Crystal Oscillators

- Standard and custom frequencies
- CMOS, LVPECL, LVDS, LP-HCSL, HCSL, CML outputs
- Packages as small as 1.6 x 1.2 mm
- Crystals up to Grade 0, 150°C

Automotive-compliant

- AEC-Qualified, manufactured in IATF 16949 certified facilities, supporting PPAP

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners. © 2023 Copyright Diodes Incorporated. All Rights Reserved. November 2023

