ZXSC440EV1 USER GUIDE

DESCRIPTION

The ZXSC440EV1 is a dedicated photoflash charger, charging an $80\mu F$ photoflash capacitor to 300V in 3.5 seconds from a 5V supply.

The flyback conversion efficiency is typically 75%, much higher than the commonly used discrete charging circuits.

The Charge pin enables the circuit to be initiated from the camera's microprocessor, using negligible current when flash is not being used.

The Ready pin signals the microprocessor when the flash is charged and ready to be fired.

FEATURES

- Charges various value photoflash capacitors
- Over 75% flyback efficiency
- · Charge and Ready pins
- Consumes only 4.5μA when not charging
- Small MSOP8 Low profile package

APPLICATIONS


- · Digital camera flash unit
- Film camera flash unit
- · Camera-phone flash unit

ORDER NUMBER

ZXSC440EV1

Please note evaluation boards are subject to availability and qualified leads.

TYPICAL APPLICATION CIRCUIT






REFERENCE DESIGN

ZXSC440EV1 is configured to the reference design below. The target application is a photoflash charger for a Xenon strobe typically used in SLR, DSC and Camera-phone flash units.

For other reference designs or further applications information please refer to the ZXSC440 datasheet.

The input voltage is typically 5V for the ZXSC440EV1 with a minimum of 4V and a maximum of 8V.

SCHEMATIC DIAGRAM




MATERIALS LIST


| REF | VALUE | PACKAGE | PART NUMBER | MANUFACTURER | NOTES |
|-------------------|--------------|---------|------------------------|----------------|--|
| U1 | | MSOP8 | ZXSC440X8 | Zetex | |
| Q1 | | SOT-23 | ZXMN6A07F | Zetex | 60V N-channel MOSFET |
| D1 ⁽¹⁾ | 200V/200mA | SOT23 | BAS21 | Philips | 200V fast rectifier diodes connected in series |
| D2 ⁽¹⁾ | 200V/200mA | SOT23 | BAS21 | Philips | 200V fast rectifier diodes connected in series |
| Tx1 | | | T-16-024A | Tokyo Coil Eng | |
| R1 | $22 m\Omega$ | 0805 | Generic | Various | |
| R2 | 10MΩ/2kV | 2010 | HVC201010MFI | Welwyn | 10ΩW/2kV 1% tolerance |
| R3 | 9.1kΩ | 1206 | Generic | Various | 1% tolerance |
| R4 | 100kΩ | 0603 | Generic | Various | 5% tolerance |
| C1 | 100μF/6V3 | 2220 | GRM43SR60J10 7ME20L | Murata | X5R dielectric, ceramic capacitor |
| C2 | 10pF/500V | 1206 | Generic | Various | Output voltage seen across capacitor |
| C3 | 10nF/6V3 | 1206 | Generic | Various | Y5V dielectric, ceramic capacitor |
| C4 | 80μF/330V | Radial | FW Series | Rubycon | Photoflash capacitor |


⁽¹⁾ Two 200V BAS21 fast rectifier diodes are connected in series for improved switching and higher efficiency.




PERFORMANCE GRAPHS









WAVEFORMS






 $V_{IN} = 4V$








 $V_{\text{IN}} = 5V\,$

 $V_{IN} = 5.5V$




 $V_{IN} = 6V$



ZXSC440EV1 OPERATION

Connection Diagram



ZXSC440EV1 Set-up and test

- 1. Connect $V_{\mbox{\scriptsize IN}}$ and GND to positive and zero volts of the power supply respectively.
- 2. Connect CHG pin to positive of power supply. If CHG pin is left floating start up cannot be guaranteed.
- 3. Connect DVM to C_{OUT} positive and GND terminals.
- 4. Connect discharge resistor (2) to DVM ensuring that the discharge resistor, SW1, is in the open position.
- 5. Set the power supply to 5V.
- 6. Turn on power supply.
- 7. The output voltage should charge up to 300V ±15V THIS IS A FUNCTIONAL EVAL BOARD.
- 8. Turn PSU off.
- 9. Switch the discharge resistor to the close position.
- 10. The output voltage should read 0V.

CAUTION: HIGH VOLTAGES ARE PRESENT

DO NOT TOUCH AND/OR SHORT CIRCUIT C_{OUT} LEADS WHEN PSU IS ON AND C_{OUT} IS CHARGED i.e. DISCHARGE RESISTOR SET TO OPEN POSITION AND/OR IS DISCONNECTED.

Discharge Resistor and SW1. (2)

The discharge resistor should be rated at $1\Omega/10$ Watts/500V and placed in series with a Single Pole Single Throw Switch (SPST) of similar rating. Attach insulated leads with 4mm plugs for connection to DVM.

(2) If connecting directly to a Xenon tube with discharge circuit the discharge resistor is not needed.


Please ensure all exposed areas of this test set-up are fully insulated from the person testing, as potentially lethal voltages are present.


ISSUE 1 - OCTOBER 2004



Low voltage operation

For operation at lower input voltages, say a Lithium-Ion battery, rated at 4.2V to 3.3V, it is possible to split the inputs so that the power line of the primary winding can be connected to VIN with the low power line Vcc of the ZXSC440 connected to a separate 5V supply. To implement this cut the bottom track from Vcc to the transformer primary winding. Connect the low voltage input directly to the transformer primary winding and the low power 5V supply to the Vcc input of the ZXSC440EV1.








Cut track on underside of PCB




Layout considerations


PCB tracks should be kept as short as possible to minimise ground bounce, and the ground pin of the device should be soldered directly to the ground plane. It is particularly important to mount the coil and the input/output capacitors close to the device to minimise parasitic resistance and inductance, which will degrade efficiency. The FB pin is a high impedance input, so PCB track lengths to this should also be kept as short as possible to reduce noise pickup. Excess capacitance from the FB pin to ground should be avoided.

Below is the recommended layout of the ZXSC440EV1.











© Zetex Semiconductors plc 2004

| Europe | Americas | Asia Pacific | Corporate Headquarters |
|-----------------------------|-----------------------------|----------------------------|-----------------------------|
| Zetex GmbH | Zetex Inc | Zetex (Asia) Ltd | Zetex Semiconductors plc |
| Streitfeldstraße 19 | 700 Veterans Memorial Hwy | 3701-04 Metroplaza Tower 1 | Lansdowne Road, Chadderton |
| D-81673 München | Hauppauge, NY 11788 | Hing Fong Road, Kwai Fong | Oldham, OL9 9TY |
| Germany | USA | Hong Kong | United Kingdom |
| Telefon: (49) 89 45 49 49 0 | Telephone: (1) 631 360 2222 | Telephone: (852) 26100 611 | Telephone (44) 161 622 4444 |
| Fax: (49) 89 45 49 49 | Fax: (1) 631 360 8222 | Fax: (852) 24250 494 | Fax: (44) 161 622 4446 |
| europe.sales@zetex.com | <u>usa.sales@zetex.com</u> | asia.sales@zetex.com | hq@zetex.com |

These offices are supported by agents and distributors in major countries world-wide.

This publication is issued to provide outline information only which (unless agreed by the Company in writing) may not be used, applied or reproduced for any purpose or form part of any order or contract or be regarded as a representation relating to the products or services concerned. The Company reserves the right to alter without notice the specification, design, price or conditions of supply of any product or service.

For the latest product information, log on to www.zetex.com



ISSUE 1 - OCTOBER 2004