



100V P-CHANNEL ENHANCEMENT MODE MOSFET

Product Summary

BV _{DSS}	R _{DS(ON)} Max	I _D Max T _A = +25°C		
4001/	1.0Ω @ V _{GS} = -10V	-0.7A		
-100V	1.45Ω @ V _{GS} = -6.0V	-0.5A		

Description and Applications

This MOSFET is designed to meet the stringent requirements of automotive applications. It is qualified to AEC-Q101, supported by a PPAP and is ideal for use in:

- DC-DC converters
- Power-management functions
- Disconnect switches
- Motor controls

Features and Benefits

- Fast Switching Speed
- Low Input Capacitance
- Low Gate Charge
- Low Threshold
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- The ZXMP10A13FQ is suitable for automotive applications requiring specific change control; this part is AEC-Q101 qualified, PPAP capable, and manufactured in IATF 16949 certified facilities.

https://www.diodes.com/quality/product-definitions/


Mechanical Data

- Package: SOT23
- Package Material: Molded Plastic, UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Annealed over Copper Leadframe; Solderable per MIL-STD-202, Method 208 @3
- Weight: 0.009 grams (Approximate)


SOT23 (Type DN)



Top View



Top View Pin Out



Equivalent Circuit


Ordering Information (Note 4)

Part Number	Paakaga	Packing		
Fait Number	Package	Qty.	Carrier	
ZXMP10A13FQTA	SOT23 (Type DN)	3000	Tape & Reel	

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + CI) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/

Marking Information



ZXMP10A13FQ Document number: DS39031 Rev. 3 - 2

1 of 8 www.diodes.com



Maximum Ratings (@ $T_A = +25$ °C, unless otherwise specified.)

Characteristic			Symbol	Value	Unit	
Drain-Source Voltage			V _{DSS}	-100	V	
Gate-Source Voltage			Vgs	±20	V	
Continuous Drain Current	V _G S = -10V	T _A = +70°C	(Note 6) (Note 6) (Note 6)	lo	-0.7 -0.5 -0.6	А
Pulsed Drain Current (Note 7)				I _{DM}	-3.1	A
Continuous Source Current (Body Diode) (Note 5)			Is	-1.1	А	
Pulsed Source Current (Body Diode) (Note 7)				Ism	-3.1	A

Thermal Characteristics


Characteristic	Symbol	Value	Unit
Power Dissipation (Note 5) Linear Derating Factor	PD	625 5	mW mW/°C
Power Dissipation (Note 6) Linear Derating Factor	PD	806 6.4	mW mW/°C
Thermal Resistance, Junction to Ambient (Note 5)	Reja	200	°C/W
Thermal Resistance, Junction to Ambient (Note 6)	Reja	155	°C/W
Thermal Resistance, Junction to Leads (Note 8)	ReJL	194	°C/W
Operating and Storage Temperature Range	T _J , T _{STG}	-55 to +150	°C

Notes:

- 5. For a device surface mounted on 25mm x 25mm FR-4 PCB with high coverage of single sided 1oz copper, in still air conditions.
- To a device surface mounted on FR-4 PCB measured at t ≤ 5 secs.
 Repetitive rating 25mm x 25mm FR-4 PCB, D = 0.05 pulse width = 10μs pulse current limited by maximum junction temperature.
 Thermal resistance from junction to solder-point (at the end of the drain lead).



Thermal Characteristics





Electrical Characteristics (@TA = +25°C, unless otherwise specified.)


Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition	
OFF CHARACTERISTICS							
Drain-Source Breakdown Voltage	BV _{DSS}	-100	_	_	V	$I_D = -250 \mu A, V_{GS} = 0 V$	
Zero Gate Voltage Drain Current	I _{DSS}	_	_	-1.0	μΑ	V _{DS} = -100V, V _{GS} = 0V	
Gate-Source Leakage	Igss	_	_	±100	nA	V _G S = ±20V, V _D S = 0V	
ON CHARACTERISTICS			•	•	•		
Gate Threshold Voltage	VGS(TH)	-2.0	_	-4.0	V	$I_D = -250\mu A$, $V_{DS} = V_{GS}$	
Static Drain Source On Registence (Note 0)	D			1.0	Ω	VGS = -10V, ID = -0.6A	
Static Drain-Source On-Resistance (Note 9)	RDS(ON)	_	_	1.45	12	Vgs = -6.0V, ID = -0.5A	
Forward Transconductance (Notes 9 and 11)	g fs	_	1.2	_	S	V _{DS} = -15V, I _D = -0.6A	
Diode Forward Voltage (Note 9)	VsD	_	-0.85	-0.95	V	T _J = +25°C, I _S = -0.75A, V _{GS} = 0V	
Reverse Recovery Time (Note 11)	trr	_	29	_	ns	T _J = +25°C, I _F = -0.9A,	
Reverse Recovery Charge (Note 11)	Qrr	_	31	_	nC	di/dt = 100A/μs	
DYNAMIC CHARACTERISTICS (Note 11)	•						
Input Capacitance	C _{iss}	_	141	_		V _{DS} = -50V, V _{GS} = 0V f = 1.0MHz	
Output Capacitance	Coss	_	13.1	_	рF		
Reverse Transfer Capacitance	C _{rss}	_	10.8	_			
Turn-On Delay Time (Note 10)	t _{D(ON)}	_	1.6	_		V_{DD} = -50V, I_{D} = -1.0A, R_{G} $\approx 6.0\Omega$, V_{GS} = -10V	
Turn-On Rise Time (Note 10)	t _R	_	2.1	_			
Turn-Off Delay Time (Note 10)	tD(OFF)	_	5.9	_	ns		
Turn-Off Fall Time (Note 10)	tF	_	3.3	_			
Total Gate Charge (Note 10)	Qg	_	1.8	_	nC	V _{DS} = -50V, V _{GS} = -5.0V, I _D = -0.6A	
Total Gate Charge (Note 10)	Qg	_	3.5	_		V _{DS} = -50V, V _{GS} = -10V, I _D = -0.6A	
Gate-Source Charge (Note 10)	Qgs	_	0.6	_	nC		
Gate-Drain Charge (Note 10)	Qgd	_	1.6	_			

Notes:

^{9.} Measured under pulsed conditions. Pulse width = 300µs. Duty cycle ≤ 2%.
10. Switching characteristics are independent of operating junction temperature.
11. For design aid only, not subject to production testing.





Typical Characteristics






Typical Characteristics (continued)





Gate-Source Voltage v Gate Charge

Test Circuits




Current regulator


Same as D.U.T

Vos

Basic gate charge waveform

Gate charge test circuit





Switching time waveforms


Switching time test circuit



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT23 (Type DN)




SOT23 Type DN					
Dim	Min	Max	Тур		
Α	0.89	1.12	1.00		
A1	0.01	0.10	0.05		
b	0.30	0.51	0.45		
С	0.08	0.20	0.10		
D	2.80	3.04	3.00		
Е	2.10	2.64	2.42		
E1	1.20	1.40	1.37		
е	0.95 REF				
e1	1.90 REF				
٦	0.25	0.60	0.30		
L1	0.45	0.62	0.54		
All Dimensions in mm					

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT23 (Type DN)



Dimensions	Value (in mm)		
С	2.0		
Х	0.8		
X1	1.35		
Y	0.9		
Y1	2.9		



IMPORTANT NOTICE

- 1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- 2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- 5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
- 9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners.

© 2024 Diodes Incorporated. All Rights Reserved.

www.diodes.com