





0.5A SBR SUPER BARRIER RECTIFIER

Product Summary (@TA= +25°C)

V _{RRM} (V)	I _O (A)	V _{F MAX} (V)	I _{R MAX} (μA)	
60	0.5	0.5	100	

Features and Benefits

- Low Forward Voltage Drop
- Low Reverse Leakage
- Excellent High Temperature Stability
- Patented Super Barrier Rectifier (SBR®) Technology
- Soft, Fast Switching Capability
- +150°C Operating Junction Temperature
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- Qualified to AEC-Q101 Standards for High Reliability
- PPAP Capable (Note 4)

Applications

- SMPS
- DC-DC Converter
- Freewheeling Diodes
- Reverse Polarity Protection

Mechanical Data

- Case: SOD123
- Case Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Leads: Solderable per MIL-STD-202, Method 208
 Lead Free Plating (Matte Tin Finish Annealed over Alloy 42
 Leadframe) (1)
- Polarity: Cathode Band
- Weight: 0.01 grams (Approximate)



Top View


Ordering Information (Note 5)

Part Number	Case	Packaging
SBR0560S1Q-7	SOD123	3000/Tape & Reel

Notes: 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant.

- 2. See http://www.diodes.com/quality/lead_free.html for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. Automotive products are AEC-Q101 qualified and are PPAP capable. Refer to https://www.diodes.com/quality/product-compliance-definitions/
- 5. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information



56 = Product Type Marking Code YM = Date Code Marking Y = Year (ex: E = 2017) M = Month (ex: 9 = September)

Date Code Key

Year	2004	2014	2015	2016	2017	2018	2019	2020	2021	2022	2023	2024
Code	R	В	С	D	Е	F	G	Н	I	J	K	L
Month	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec
WOULD	Jan	1 60	IVICII	Αþi	iviay	Juli	Jui	Aug	Seb	OCI	1404	Dec



Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Single phase, half wave, 60Hz, resistive or inductive load.

For capacitive load, derate current by 20%.

Characteristic	Symbol	Value	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	V _{RRM} V _{RWM} V _{RM}	60	٧
Average Rectified Output Current	lo	500	mA
Non-Repetitive Peak Forward Surge Current 8.3ms Single Half Sine-Wave Superimposed on Rated Load	I _{FSM}	15	Α

Thermal Characteristics

Characteristic	Symbol	Value	Unit
Thermal Resistance Junction to Ambient Air (Note 6) Thermal Resistance Junction to Ambient Air (Note 7)	$R_{ heta JA} \ R_{ heta JA}$	305 271	°C/W
Operating and Storage Temperature Range	T _J , T _{STG}	-65 to +150	°C

Electrical Characteristics (@TA = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
Forward Voltage (Per Diode)	V _F	-	- 0.44 -	0.44 0.50 0.46	٧	I _F = 0.25A, T _J = +25°C I _F = 0.5A, T _J = +25°C I _F = 0.5A, T _J = +125°C
Leakage Current (Note 8)	I _R	-	-	100 25	μA mA	$V_R = 60V, T_J = +25^{\circ}C$ $V_R = 60V, T_J = +125^{\circ}C$

Notes:


^{6.} Part mounted on FR-4 board with recommended pad layout, which can be found on our website at http://www.diodes.com/package-outlines.html.


^{7.} Part mounted on Polymide board with recommended pad layout, which can be found on our website at http://www.diodes.com/nackage.outlines.html


http://www.diodes.com/package-outlines.html.


8. Short duration pulse test used to minimize self-heating effect.














SBR0560S1Q


Document number: DS38742 Rev. 3 - 2



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOD123




SOD123							
Dim	Min	Max	Тур				
Α	1.00	1.35	1.05				
A1	0.00	0.10	0.05				
b	0.52	0.62	0.57				
С	0.10	0.15	0.11				
D	1.40	1.70	1.55				
E	2.55	2.85	2.65				
He	3.55	3.85	3.65				
L	0.25	0.40	0.30				
а	00	8°					
All Dimensions in mm							

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOD123



Dimensions	Value (in mm)
Х	0.900
X1	4.050
Y	0.950



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2017, Diodes Incorporated

www.diodes.com