






N-CHANNEL ENHANCEMENT MODE MOSFET


Features

- Low On-Resistance
- Low Gate Threshold Voltage
- Low Input Capacitance
- Fast Switching Speed
- Low Input/Output Leakage
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- Qualified to AEC-Q101 Standards for High Reliability
- PPAP Capable (Note 4)

Mechanical Data

- Case: SOT23
- Case Material: Molded Plastic.
 - UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Matte Tin Finish Annealed over Alloy 42 Leadframe (Lead Free Plating).
 - Solderable per MIL-STD-202, Method 208 @3
- Terminal Connections: See Diagram
- Weight: 0.008 grams (Approximate)





Top View

Equivalent Circuit

Top View

Ordering Information (Note 5)


Part Number	Case	Packaging
MMBF170Q-7-F	SOT23	3,000/Tape & Reel
MMBF170Q-13-F	SOT23	10,000/Tape & Reel

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant.
- 2. See http://www.diodes.com/quality/lead_free.html for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
 4. Automotive products are AEC-Q101 qualified and are PPAP capable. Automotive, AEC-Q101 and standard products are electrically and thermally the
- 4. Automotive products are AEC-Q101 qualified and are PPAP capable. Automotive, AEC-Q101 and standard products are electrically and thermally the same, except where specified. For more information, please refer to http://www.diodes.com/quality/product_grade_definitions/.
- 5. For packaging details, go to our website at http://www.diodes.com/products/packages.html.

Marking Information

SOT23



K6Z = Product Type Marking Code YM = Date Code Marking Y = Year (ex: A = 2014) M = Month (ex: 9 = September)

Date Code Key

Year	1998	1999	2000	2001	2002		2014	2015	2016	2015	2016	2017	2018	2019	2020
Code	J	Κ	L	М	N		В	С	D	С	D	Е	F	G	Н
Month	Jan	Fe	b	Mar	Apr	May	Ju	n	Jul	Aug	Sep	Oc	t	Nov	Dec
Code	1	2		3	4	5	6		7	8	9	0		N	D



Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Characteristic		Symbol	Value	Units
Drain-Source Voltage		V_{DSS}	60	V
Drain-Gate Voltage $R_{GS} \le 1.0 M\Omega$		V_{DGR}	60	V
Gate-Source Voltage	Continuous Pulsed	V_{GSS}	±20 ±40	V
Drain Current (Note 6)	Continuous Pulsed	I _D	500 800	mA

Thermal Characteristics (@TA = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Units
Total Power Dissipation (Note 6)	P_{D}	300 1.80	mW mW/°C
Thermal Resistance, Junction to Ambient	$R_{ heta JA}$	417	K/W
Operating and Storage Temperature Range	T _J , T _{STG}	-55 to +150	°C

Electrical Characteristics (@TA = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition	
OFF CHARACTERISTICS (Note 7)							
Drain-Source Breakdown Voltage	BV _{DSS}	60	70	_	V	$V_{GS} = 0V, I_D = 100\mu A$	
Zero Gate Voltage Drain Current	I _{DSS}	_	_	1.0	μΑ	V _{DS} = 60V, V _{GS} = 0V	
Gate-Body Leakage	I _{GSS}	_	_	±10	nA	$V_{GS} = \pm 15V, V_{DS} = 0V$	
ON CHARACTERISTICS (Note 7)							
Gate Threshold Voltage	V _{GS(th)}	8.0	2.1	3.0	V	$V_{DS} = V_{GS}, I_{D} = 250 \mu A$	
Static Drain-Source On-Resistance	R _{DS (ON)}			5.0 5.3	Ω	$V_{GS} = 10V, I_D = 200mA$ $V_{GS} = 4.5V, I_D = 50mA$	
Forward Transconductance	9 FS	80	_	_	mS	$V_{DS} = 10V, I_D = 0.2A$	
DYNAMIC CHARACTERISTICS				-			
Input Capacitance	C _{iss}		22	40	pF		
Output Capacitance	Coss	_	11	30	pF	$V_{DS} = 10V, V_{GS} = 0V, f = 1.0MHz$	
Reverse Transfer Capacitance	Crss	_	2.0	5.0	pF		
SWITCHING CHARACTERISTICS							
Turn-On Time	t _{on}			10	ns	$V_{DD} = 25V, I_D = 0.5A,$	
Turn-Off Time	t _{off}			10	ns	V_{GS} = 10V, R_{GEN} = 50 Ω	


Notes:

^{6.} Device mounted on FR-4 PCB 1.0 x 0.75 x 0.062 inch pad layout as shown on Diodes, Inc. suggested pad layout AP02001, which can be found on our website at http://www.diodes.com

website at http://www.diodes.com.

7. Short duration pulse test used to minimize self-heating effect.





T_j = 25°C

| T_j = 25°C |
|





Fig. 5 Max Power Dissipation vs. Ambient Temperature



Package Outline Dimensions

Please see AP02002 at http://www.diodes.com/datasheets/ap02002.pdf for the latest version.




SOT23							
Dim	Min	Тур					
Α	0.37	0.51	0.40				
В	1.20	1.40	1.30				
C	2.30	2.50	2.40				
D	0.89	1.03	0.915				
F	0.45	0.60	0.535				
G	1.78	2.05	1.83				
H	2.80	3.00	2.90				
7	0.013	0.10	0.05				
K	0.890	1.00	0.975				
K1	0.903	1.10	1.025				
L	0.45	0.61	0.55				
L1	0.25	0.55	0.40				
M	0.085	0.150	0.110				
а	8°						
All Dimensions in mm							

Suggested Pad Layout

Please see AP02001 at http://www.diodes.com/datasheets/ap02001.pdf for the latest version.

SOT23



Dimensions	Value (in mm)
Z	2.9
Х	0.8
Y	0.9
С	2.0
F	1.35

January 2015



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical. life support devices or systems.

Copyright © 2015, Diodes Incorporated

www.diodes.com