



WHITE LED STEP-UP CONVERTER

AP3031

Description

The DIODES[™] AP3031 is an inductor-based DC/DC boost converter designed to drive LED arrays. 1.4A switching current allows AP3031 to be used in different 7' to 10' LCD panel backlights (3*13 LED arrays typically).

A constant frequency 1MHz PWM control scheme is employed in this IC, which means tiny external components can be used. Specifically, 1mm tall 4.7μ H inductor and 0.47μ F output capacitor for the typical application is sufficient.

The over output voltage protection is equipped in AP3031, which protects the IC under open load condition. The AP3031 includes UVLO, soft-start, current limit and OTSD to protect the circuit.

The AP3031 is available in standard SOT-23-6 package.


Features

- Up to 92% Efficiency (V_{IN} = 9V, I_{OUT} = 260mA)
- Up to 84% Efficiency (V_{IN} = 5V, I_{OUT} = 260mA)
- Fast 1MHz Switching Frequency
- Wide Input Voltage Range: 2.7V to 16V
- Low 200mV Feedback Voltage
- Output Overvoltage Protection
- Cycle by Cycle Current Limit: 1.4A
- Built-in Soft-Start
- Built-in Standby Mode to Achieve High Frequency PWM Dimming
- Built-in Thermal Shutdown Function
- Undervoltage Lockout
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please <u>contact us</u> or your local Diodes representative. <u>https://www.diodes.com/quality/product-definitions/</u>

Notes:

- No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
 See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds .

Pin Assignments




Applications


- 7' to 10' LCD panels
- Digital photo frames
- GPS receivers
- EPC
- PDVD




Typical Applications Circuit



3 x 3 WLEDs



Booster for LNB Application (Note 4)



Booster for Portable Charger Application (Note 4)


Note: 4. V_{OUT} = (1+R1/R2)*V_{FB}.



Pin Description

Pin Number Pin Name		Function		
1	SW	Switch Pin. Connect external inductor and Schottky.		
2	GND	Ground Pin.		
3	FB	Voltage Feedback Pin. Reference voltage is 200mV.		
4	CTRL	 Enable and Dimming Control Pin. Connect to a high input to enable the IC or a low input to disable the IC. If logic low time is more than about 0.7ms and then the IC is enabled, the AP3031 will soft start to protect system departments. If logic low time is less than about 0.7ms and then the IC is enabled, the AP3031 will hold on standby mode and start directly to achieve high frequency dimming. 		
5	OV	Overvoltage Protection Input Pin. Connect to the output directly. On OVP condition, the output voltage will be clamped.		
6	VIN	Input Supply Pin. Must be locally bypassed.		

Functional Block Diagram



Absolute Maximum Ratings (Note 5)

Symbol	Parameter	Rating	Unit
VIN	Input Voltage	20	V
Vsw	SW Pin Voltage	38	V
V _{FB}	Feedback Voltage	20	V
Vctrl	CTRL Pin Voltage	20	V
θ」Α	Thermal Resistance (Junction to Ambient, No Heat Sink)	265	°C/W
TJ	Operating Junction Temperature	+150	°C
T _{STG}	Storage Temperature Range	-65 to +150	°C
TLEAD	Lead Temperature (Soldering, 10sec)	+260	°C
_	ESD (Machine Model)	600	V
_	ESD (Human Body Model)	4000	V

Note: 5. Stresses greater than those listed under *Absolute Maximum Ratings* can cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions* is not implied. Exposure to *Absolute Maximum Ratings* for extended periods can affect device reliability.



Recommended Operating Conditions

Symbol	Parameter	Min	Мах	Unit
T _{OP}	Operating Temperature Range	-40	+85	°C
V _{IN}	Input Voltage	2.7	16	V
Vctrl	CTRL Pin Voltage	—	16	V

Electrical Characteristics ($@V_{IN} = 5.0V$, $V_{CTRL} = 5.0V$, $T_A = +25^{\circ}C$, unless otherwise specified.)


Symbol	Parameter	Conditions	Min	Тур	Max	Unit
Vin	Operating Voltage	—	2.7	_	16	V
Vfb	Feedback Voltage (Note 6)	$I_{OUT} = 20mA, 3 LEDs$ $T_A = -40^{\circ}C$ to +85°C	188	200	212	mV
IFB	FB Pin Bias Current	—	—	35	100	nA
lq	Quiescent Current	V _{FB} = V _{IN} , No Switching	3.0	4.0	5.0	mA
ISHDN	Shutdown Quiescent Current	V _{CTRL} = 0V	20	50	80	μA
f	Switching Frequency	—	0.75	1	1.3	MHz
DMAX	Maximum Duty Cycle	—	90	93	_	%
Ilimit	Switch Current Limit (Note 7)	D = 60%	1.2	1.4	_	А
VCESAT	Switch VCE Saturation Voltage	Isw = 0.6A	_	300	—	mV
_	Switch Leakage Current	Vsw = 16V	_	0.01	5	μA
		Active High	1.8	—	—	
Vctrl	CTRL Pin Voltage	Active Low	_	_	0.5	V
ICTRL	CTRL Pin Bias Current	—	35	60	85	μA
Vovp	OVP Voltage	_	15.5	17.5	19.5	V
tss	Soft-Start Time	—	_	250	—	μs
tsтв	Standby Time		—	0.7	_	ms
Totsd	Thermal Shutdown		<u> </u>	+155	—	°C
θJC	Thermal Resistance (Junction to Case)	_	-	60	_	°C/W

Notes:

6. The bold type specifications of full temperature range are guaranteed by design (GBD).7. The switch current limit is related to duty cycle. Please refer to Figure Switch Current Limit vs. Duty Cycle for detail.




Performance Characteristics (WLED forward voltage (VF) = 3.2V at IF = 20mA, unless otherwise noted.)




Efficiency vs. Output Current


Efficiency vs. Input Voltage




Minimum Operating Voltage vs. Temperature




Shutdown Quiescent Current vs. Input Voltage



Quiescent Current vs. Input Voltage




CTRL Pin Voltage vs. Temperature






Performance Characteristics (WLED forward voltage (VF) = 3.2V at IF = 20mA, unless otherwise noted.) (continued)




CTRL Pin Current vs. CTRL Pin Voltage


Feedback Voltage vs. Temperature




Frequency vs. Temperature




Frequency vs. Input Voltage



OVP Voltage vs. Temperature




Switch Current Limit vs. Duty Cycle





AP3031

Performance Characteristics (WLED forward voltage (VF) = 3.2V at IF = 20mA, unless otherwise noted.) (continued)



Switch Saturation Voltage vs. Switch Current

Case Temperature vs. Output Current

Application Information

Operation

The AP3031 is a boost DC-DC converter which uses a constant frequency, current mode control scheme to provide excellent line and load regulation. Operation can be best understood by referring to *Function Block Diagram* and *Typical Applications Circuit*.

At the start of each oscillator cycle, switch Q1 turns on. The switch current will increase linearly. The voltage on sense resistor is proportional to the switch current. The output of the current sense amplifier is added to a stabilizing ramp and the result is fed into the non-inversion input of the PWM comparator A2. When this voltage exceeds the output voltage level of the error amplifier A1, the switch is turned off.

It is clear that the voltage level at inversion input of A2 sets the peak current level to keep the output in regulation. This voltage level is the output signal of error amplifier A1, and is the amplified signal of the voltage difference between feedback voltage and reference voltage of 200mV. So, a constant output current can be provided by this operation mode.

LED Current Control

Refer to *Typical Applications Circuit*, the LED current is controlled by the feedback resistor R_{ISET}. LEDs' current accuracy is determined by the feedback voltage and resistor R_{ISET}, so the precise resistors are preferred. The resistance of R_{ISET} is in inverse proportion to the LED current since the feedback reference is fixed at 200mV. The relation for R_{ISET} and LED current (I_{LED}) can be expressed as below:

$$R_{ISET} = \frac{200mV}{I_{LED}}$$


Overvoltage Protection


The AP3031 has an internal open load protection circuit. When the LEDs are disconnected from circuit or fail open, the output voltage is clamped at about 17.5V. The AP3031 will switch at a low frequency, and minimize current to avoid input voltage drop.

Soft-Start

The AP3031 has an internal soft start circuit to limit the inrush current during startup. If logic low time on CTRL pin is more than about 0.7ms and then the IC is enabled, the AP3031 will start smoothly to protect the supplier. The time of startup is controlled by internal soft-start capacitor. For details please refer to the Figure of Soft-Start Waveform.









Standby and Dimming

To avoid audio noise and achieve high frequency dimming, AP3031 is equipped with standby function. If logic low time on CTRL pin is less than about 0.7ms and then the IC is enabled, the AP3031 will hold on standby mode and start directly to achieve high frequency dimming. For details please refer to the Figure of Standby Waveform.






Two typical types of dimming control circuit are present as below. First, controlling CTRL pin voltage to change operation state is a good choice. Second, changing the feedback voltage to get appropriate duty and luminous intensity is also useful.


(1) Adding a Control Signal to CTRL Pin

Add a PWM signal to CTRL pin directly, the AP3031 is turned on and off by this signal. When the PWM frequency is lower than 1kHz (Typ.), the IC works in the soft-start mode to dimming the light. On contrary, when the PWM frequency is higher than 1kHz (Typ.), the IC works in the standby mode: the converter ceaselessly switches off and directly starts to achieve light dimming. This standby function allows AP3031 to support high frequency dimming (up to 25kHz or higher) to avoid audio noise. For more details please refer to the Figure of Dimming Control Using a PWM Signal in CTRL Pin and the Figure of High Frequency (25kHz) Dimming Waveform.



Dimming Control Using a PWM Signal in CTRL Pin






Time 20µs/div

High Frequency (25kHz) Dimming Waveform


(2) Changing the Effective Feedback Voltage

There are two popular methods to change the effective feedback voltage.

First, adding a constant DC voltage through a resistor divider to FB pin can control the dimming. Changing the DC voltage or resistor between the FB pin and the DC voltage can get appropriate luminous intensity. Comparing with all kinds of PWM signal control, this method features a stable output voltage and LEDs current. Please refer to the Figure of Dimming Control Using DC Voltage.




Second, using a filtered PWM signal can do it. The filtered PWM signal can be considered as a varying and adjustable DC voltage. Please refer to the Figure of Dimming Control Using Filtered PWM Voltage.



Dimming Control Using Filtered PWM Voltage




Ordering Information



Part Number	Package	Temperature Range	Identification Code	Packing		
Fait Nulliper	Гаскауе			Qty.	Carrier	
AP3031KTR-G1	SOT-23-6	-40 to +85°C	GEC	3000	Tape & Reel	

Marking Information




Part Number	Package	Identification Code	
AP3031KTR-G1	SOT-23-6	GEC	



Package Outline Dimensions (All dimensions in mm(inch).)

Please see http://www.diodes.com/package-outlines.html for the latest version.






AP3031

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.



Dimensions	Z	G X		Y E	
	(mm)/(inch)	(mm)/(inch) (mm)/(inch)		(mm)/(inch) (mm)/(inch)	
Value	3.600/0.142	1.600/0.063	0.700/0.028	1.000/0.039	0.950/0.037

Mechanical Data

- Moisture Sensitivity: Level 3 per JESD22-A113
- Terminals: Matte Tin Plated Leads, Solderable per M2003 JESD22-B102 (3)
- Weight: 0.016 grams (Approximate)



AP3031

IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

Diodes' products are provided subject Diodes' Standard Terms and Conditions of to Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. DIODES is a trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners. © 2022 Diodes Incorporated. All Rights Reserved.

www.diodes.com