

Features

- Fast Switching Speed
- Surface Mount Package Ideally Suited for Automated Insertion
- For General Purpose Switching Applications
- High Reverse Breakdown Voltage
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change
- control (i.e.: parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please refer to the related automotive grade (Q-suffix) part. A listing can be found at

https://www.diodes.com/products/automotive/automotiveproducts/.

• This part is qualified to JEDEC standards (as references in AEC-Q) for High Reliability.

https://www.diodes.com/guality/product-definitions/

Mechanical Data

- Package: SOD323
- Package Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminal Connections: Cathode Band, See Page 2
- Terminals: Matte Tin Finish Annealed over Alloy 42 Leadframe. Solderable per MIL-STD-202, Method 208 (3)
- Weight: 0.004 grams (Approximate)

SOD323



Top View



Ordering Information (Note 4)

Orderable Part Number	Baakaga	Packing			
Orderable Fart Number	Package	Quantity Carrier			
BAV19WS-7-F	SOD323	3,000	Tape & Reel		
BAV20WS-7-F	SOD323	3,000	Tape & Reel		
BAV21WS-7-F	SOD323	3,000	Tape & Reel		
BAV21WS-13-F	SOD323	10,000	Tape & Reel		
BAV21WSQ-7-F	SOD323	3,000	Tape & Reel		

Notes:

No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.</p>

4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information



XX = Product Type Marking Code BAV19WS Marking: T3 BAV20WS Marking: T3 BAV21WS Marking: T3



Maximum Ratings (@ T_A = +25°C, unless otherwise specified.)

Characteristic		Symbol	BAV19WS	BAV20WS	BAV21WS	Unit
Repetitive Peak Reverse Voltage		V _{RRM}	120	200	250	V
Working Peak Reverse Voltage DC Blocking Voltage		V _{RWM} VR	100	150	200	V
RMS Reverse Voltage		V _{R(RMS)}	71	106	141	V
Forward Continuous Current (Note 5)		I _{FM}	250			mA
Average Rectified Output Current (Note 5)		I _O	200			mA
Non-Repetitive Peak Forward Surge Current	@ t = 1.0µs @ t = 100µs @ t = 10ms	I _{FSM}	9.0 3.0 1.7			A
Repetitive Peak Forward Surge Current		I _{FRM}	625			mA

Thermal Characteristics

Characteristic	Symbol	Value	Unit
Power Dissipation	PD	200	mW
Thermal Resistance Junction to Ambient Air (Note 5)	R _{0JA}	625	°C/W
Operating and Storage Temperature Range	T_J , T_STG	-55 to +150	°C


Electrical Characteristics (@ T_A = +25°C, unless otherwise specified.)


Characteristic		Symbol	Min	Max	Unit	Test Condition
Reverse Breakdown Voltage (Note 6)	BAV19WS BAV20WS BAV21WS	V _{(BR)R}	120 200 250	_	V	I _R = 100μA
Forward Voltage		VF	—	1.0 1.25	V	I _F = 100mA I _F = 200mA
Peak Reverse Current @ Rated DC Blocking Voltage (Note 6)		I _R	_	100 15	nΑ μΑ	T _J = +25°C T _J = +100°C
Total Capacitance		CT		5.0	pF	V _R = 0, f = 1.0MHz
Reverse Recovery Time		t _{RR}	_	50	ns	$I_F = I_R = 30$ mA, $I_{RR} = 0.1 \times I_R$, $R_L = 100\Omega$

 Device mounted on FR-4 substrate PC board, 2oz copper, with 1inch square copper pad layout.
Short duration pulse test used to minimize self-heating effect. Notes:



BAV19WS - BAV21WS








Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.




SOD323						
Dim	Min	Max	Тур			
A1		0.10	0.05			
A2	1.00	1.10	1.05			
b	0.25	0.35	0.30			
c	0.10	0.15	0.11			
D	1.20	1.40	1.30			
ш	1.60	1.80	1.70			
He	2.30	2.70	2.50			
L	0.20	0.40	0.30			
а	0°	8°	_			
All Dimensions in mm						

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOD323

SOD323



Dimensions	Value (in mm)
Х	0.590
X1	2.700
Y	0.450



IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

5 Diodes' provided to Diodes' Standard Terms and Conditions of Sale products are subject (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners. © 2023 Diodes Incorporated. All Rights Reserved.

www.diodes.com