

### AP7387Q AUTOMOTIVE COMPLIANT WIDE INPUT VOLTAGE RANGE 150mA ULDO REGULATOR

### Description

The DIODES<sup>™</sup> AP7387Q series is a wide input voltage range (60V), low quiescent current, high PSRR linear regulator able to driver 150mA output current.

The AP7387Q features a very fast line/load transient response against the rapid input voltage and load current changes. The IC consists of a voltage reference, an error amplifier, a resistor network for setting output voltage, a current limit circuit for current protection, short-circuit and thermal shutdown protection.

The AP7387Q has 3.0V, 3.3V, 3.6V, and 5V fixed output voltage versions, and is available in the SOT89 and U-DFN2020-6 (SWP) (Type UXC) packages.

### **Features**

- Wide Input Voltage Range: 5V to 60V
- Maximum Output Current: 150mA
- Dropout Voltage:
  V<sub>DROP</sub> = 700mV @lout = 100mA (Typ.)
  V<sub>DROP</sub> = 1100mV @lout = 150mA (Typ.)
- Low Quiescent Current: 2µA (Typ.)
- High Output Voltage Accuracy: ±2%
- High PSRR: 70dB @1kHz
- Excellent Line/Load Regulation
- Thermal Shutdown Function
- Short Current Protection Function
- Output Current Limit
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen- and Antimony-Free. "Green" Device (Note 3)
- The AP7387Q is suitable for automotive applications requiring specific change control; this part is AEC-Q100 qualified, PPAP capable, and manufactured in IATF 16949 certified facilities.

https://www.diodes.com/guality/product-definitions/


Notes:

(Top View)



SOT89

(Top View)



### U-DFN2020-6 (SWP) (Type UXC)

Future Product

### Applications

- Powering MCUs and CAN/LIN transceivers
- Automotive head units

**Pin Assignments** 


- EV and HEV battery management systems
- Body control modules
- Transmission control units (TCUs)

No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
 See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.



# **Typical Applications Circuit**




# **Pin Descriptions**

Pir	n Number		
SOT89	U-DFN2020-6 (SWP) (Type UXC)	Pin Name	Function
3	1	VIN	Input voltage
2, TAB	3, 4	GND	Ground
_	2, 5	NC	Not connected internally, recommend connection to GND to maximize PCB copper for thermal dissipation.
1	6	VOUT	Regulated output voltage
	EP	Exposed Pad	In PCB layout, prefer to use large copper area to cover this pad for better thermal dissipation, then connect this area to GND or leave it open. However, do not use it as GND electrode function alone.



# **Functional Block Diagram**



Symbol	Parameter	Rating		Unit
VIN	Supply Input Voltage	-0.3 to 80	-0.3 to 80	
Vout	Regulated Output Voltage	-0.3 to 6		V
Vout_Vin	Vout to Vin	-35 to 0.3		V
Іоит	Output Current	Internally Limited		mA
TLEAD	Lead Temperature (Soldering, 10sec)	+260		°C
TJ	Operating Junction Temperature	+150		°C
TA	Operating Ambient Temperature	-40 to +125		°C
0		SOT89	78.6	2011
θја	Thermal Resistance Junction to Ambient $(\theta_{JA})$	U-DFN2020-6 (SWP) (Type UXC)	47.9	°C/W
T <sub>STG</sub>	Storage Temperature Range	-40 to +150		°C
CDM	ESD (Change Device Model)	1.5		kV
HBM	ESD (Human Body Model)	4		kV

### Absolute Maximum Ratings (Note 4) (@TA = -40°C to +125°C, unless otherwise specified.)

Note:

4. a). Stresses greater than those listed under Absolute Maximum Ratings can cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions is not implied. Exposure to Absolute Maximum Ratings for extended periods can affect device reliability.

b). Ratings apply to ambient temperature at +25°C. The JEDEC STD.51 High-K board design used to derive this data was a 3 inch x 3 inch multilayer board with 1oz. internal power and ground planes and 2oz. copper traces on the top and bottom of the board.

### **Recommended Operating Conditions**


Symbol	Parameter	Min	Тур	Max	Unit
Vin	Supply Input Voltage	5.0	—	60	V
Vout	Supply Output Voltage	3.0	—	5	V
TJ	Operating Junction Temperature	-40	—	+125	°C
Cin	Input Capacitor	—	1	—	μF
Соит	Output Capacitor	1	10	—	μF




Symbol	Parameter	Test Conditions	Min	Тур	Max	Unit	
V <sub>IN</sub>	Input Voltage	—	5.0		60	V	
Ignd	Quiescent Current	V <sub>IN</sub> = 12V, No Load	_	2	5	μA	
Vout	Output Voltage	V <sub>IN</sub> = 12V, I <sub>OUT</sub> = 10mA	Voutx98%		Voutx102%	V	
IOUT_MAX	—	—	—	150	—	mA	
		$I_{OUT} = 50 \text{mA}, V_{OUT} = V_{OUTNOM} - 0.1 \text{V}$	—	350	500	mV	
VDROP Dropout Voltage	Dropout Voltage	IOUT = 100mA, VOUT = VOUTNOM $- 0.1V$	—	700	1000	mV	
		IOUT = 150mA, VOUT = VOUTNOM $- 0.1V$	—	1100	1600	mV	
ΔVout(Δlout)	Load Regulation	$V_{IN} = 12V, 1mA \le I_{OUT} \le 150mA$	_	0.02	0.03	%/mA	
$\Delta V_{OUT}/\Delta V_{IN}$	Line Regulation	$V_{OUTNOM} + 0.5V \le V_{IN} \le 60V$ IOUT = 1mA	_	0.01	0.02	%/V	
ILIMIT	Current Limit	_	_	250	—	mA	
Totsd	Thermal Shutdown Temperature	—	_	+150	—	°C	
THYOTSD	Thermal Shutdown Hysteresis	—	_	+30	—	°C	
PSRR	Power Supply Rejection Ratio	V <sub>IN</sub> = 12V, Iout = 1mA Vout = 3.3V @1kHz	—	70	_	dB	
0		SOT89	_	25.1	_	•CAN	
θις	Thermal Resistance Junction to Case ( $\theta_{JC}$ )	U-DFN2020-6 (SWP) (Type UXC)	_	15.5	—	°C/W	




### **Performance Characteristics**









## **Typical Characteristics**










# Typical Characteristics (continued)













Current Limit vs. Input Voltage


### Typical Characteristics (continued)









## Typical Characteristics (continued)




Time:200µs/div







# Typical Characteristics (continued)





### **Application Information**

#### **Output Capacitor**

An output capacitor is required for the stability of the LDO. The recommended minimum output capacitance is 1µF. A ceramic capacitor is recommended with the temperature characteristics of X7R or X5R. Higher capacitance values help to improve load/line transient response. The output capacitance may be increased to keep low undershoot/overshoot. Place the output capacitor as close as possible to VOUT and GND pins.

#### Input Capacitor

A 1µF ceramic capacitor is recommended to connect between VIN and GND pins to decouple input power supply glitch and noise. The amount of the capacitance may be increased without limit. This input capacitor must be located as close as possible to the device to ensure input stability and less noise. For PCB layout, a wide copper trace is required for both VIN and GND.

#### **Current-Limit and Short-Circuit Protection**

When the output current at VOUT pin is higher than the current-limit threshold or the VOUT pin is directly shorted to GND, current-limit protection will be triggered and clamp the output current at a pre-designed level to prevent overcurrent and thermal damage.


#### **Thermal Protection**

The AP7387 has internal thermal sense and protection circuits. When excessive power dissipation happens on the device, such as short circuit at the output pin or very heavy load current with a large voltage drop across the device, the internal thermal protection circuit will be triggered, and it will shut down the power MOSFET to prevent the LDO from damage. As soon as the excessive thermal condition is removed and the temperature of the device drops down, the thermal protection circuit will release the control of the power MOSFET and the LDO device will return to normal operation.

#### Layout Considerations

For good ground loop and stability, the input and output capacitors should be located close to the input, output, and ground pins of the device. The regulator ground pin should be connected to the external circuit ground to reduce voltage drop caused by trace impedance. Ground plane is generally used to reduce trace impedance. Wide trace should be used for large current paths from V<sub>IN</sub> to V<sub>OUT</sub>, and load circuit.

### **Ordering Information**




Part Number	Part Number Suffix	art Number Suffix Package Package Coc		Port Number Suffix Backage	Baakaga Cada	Pac	king
		Fackage	Package Code	Qty.	Carrier		
AP7387Q-XXY-13	-13	SOT89	Y	2,500	13" Tape & Reel		
AP7387Q-XXFDCW-7	-7	U-DFN2020-6 (SWP) (Type UXC)	FDCW	3,000	7" Tape & Reel		



## **Marking Information**

### (1) SOT89



Part Number	Package	Identification Code
AP7387Q-30Y-13	SOT89	H7AQ
AP7387Q-33Y-13	SOT89	H7BQ
AP7387Q-36Y-13	SOT89	H7CQ
AP7387Q-50Y-13	SOT89	H7DQ

#### (2) U-DFN2020-6 (SWP) (Type UXC)

(Top View)

<u>XXXX</u>

<u>Y W X</u>

<u>XXXX</u> :	Identification	Code
---------------	----------------	------


- <u>Y</u> : Year : 0 to 9 (ex: 2 = 2022)
- $\underline{W}$  : Week : A to Z : week 1 to 26; a to z : week 27 to 52; z represents week 52 and 53
- X : Internal Code

Part Number	Package	Identification Code
AP7387Q-30FDCW-7	U-DFN2020-6 (SWP) (Type UXC)	H7AQ
AP7387Q-33FDCW-7	U-DFN2020-6 (SWP) (Type UXC)	H7BQ
AP7387Q-36FDCW-7	U-DFN2020-6 (SWP) (Type UXC)	H7CQ
AP7387Q-50FDCW-7	U-DFN2020-6 (SWP) (Type UXC)	H7DQ



# **Package Outline Dimensions**


Please see http://www.diodes.com/package-outlines.html for the latest version.



SOT89					
Dim	Min	Max	Тур		
Α	1.40	1.60	1.50		
В	0.50	0.62	0.56		
B1	0.42	0.54	0.48		
С	0.35	0.43	0.38		
D	4.40	4.60	4.50		
D1	1.62	1.83	1.733		
D2	1.61	1.81	1.71		
Е	2.40	2.60	2.50		
E2	2.05	2.35	2.20		
е	-	-	1.50		
Н	3.95	4.25	4.10		
H1	2.63	2.93	2.78		
L	0.90	1.20	1.05		
L1	0.327	0.527	0.427		
Z	0.20	0.40	0.30		
All	Dimen	sions i	in mm		

U-DFN2020-6 (SWP) (Type UXC)

BOTTOM VIEW




U	U-DFN2020-6 (SWP) (Type UXC)					
Dim	Min	Max	Тур			
Α	0.57	0.63	0.60			
A1	0.00	0.05	0.02			
A3		_	0.13			
b	0.25	0.35	0.30			
D	1.95	2.075	2.00			
D2	1.55	1.75	1.65			
Е	1.95	2.075	2.00			
E2	0.86	1.06	0.96			
е			0.65			
L	0.25	0.35	0.30			
z			0.20			
aaa		0.25				
bbb	0.10					
CCC	0.10					
All	Dimens	sions in	mm			



# **Suggested Pad Layout**


Please see http://www.diodes.com/package-outlines.html for the latest version.



Dimensions	Value (in mm)
С	1.500
G	0.244
Х	0.580
X1	0.760
X2	1.933
Ŷ	1.730
Y1	3.030
Y2	1.500
Y3	0.770
Y4	4.530

#### U-DFN2020-6 (SWP) (Type UXC)

SOT89



Dimensions	Value (in mm)
С	0.650
Х	0.350
X1	1.650
X2	1.700
Y	0.525
Y1	1.010
Y2	2.400

### **Mechanical Data**

- Moisture Sensitivity: Level 1 Per J-STD-020
- Terminals:
  - SOT89: Finish Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 (3)
  - U-DFN2020-6 (SWP) (Type UXC): Finish NiPdAu over Copper Leads, Solderable per MIL-STD-202, Method 208 ④
- Weight:
  - SOT89: 0.056 grams (Approximate)
  - U-DFN2020-6 (SWP) (Type UXC): 0.007 grams (Approximate)



#### IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

Diodes' products are provided subject Diodes' Standard Terms and Conditions of to Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

9. This Notice may be periodically updated with the most recent version available at <a href="https://www.diodes.com/about/company/terms-and-conditions/important-notice">https://www.diodes.com/about/company/terms-and-conditions/important-notice</a>

DIODES is a trademark of Diodes Incorporated in the United States and other countries. The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. © 2022 Diodes Incorporated. All Rights Reserved.

#### www.diodes.com