



40V N-CHANNEL ENHANCEMENT MODE MOSFET

Product Summary

BV _{DSS}	Rds(on)	I _D T _A = +25°C
401/	30mΩ @V _{GS} = 10V	9.6A
40V	50mΩ @V _{GS} = 4.5V	7.4A

Description and Applications

This MOSFET has been designed to minimize the on-state resistance RDS(ON)) yet maintain superior switching performance, making it ideal for high efficiency power management applications.

- Backlighting
- DC-DC Converters
- · Power Management Functions

Features and Benefits


- Low On-Resistance
- · Fast Switching Speed
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e.: parts qualified to AEC-Q100/101/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please refer to the related automotive grade (Q-suffix) part.
 A listing can be found at

https://www.diodes.com/products/automotive/automotive-products/.

- This part is qualified to JEDEC standards (as references in AEC-Q) for High Reliability.
 - https://www.diodes.com/quality/product-definitions/
- An Automotive-Compliant Part is Available Under Separate Datasheet (<u>DMN4030LK3Q</u>)


Mechanical Data


- Case: TO252
- Case Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Matte Tin Finish Annealed over Copper Leadframe.
 Solderable per MIL-STD-202, Method 208 (3)





Top View





Equivalent Circuit


Ordering Information (Note 4)

Part Number	Case	Packaging
DMN4030LK3-13	TO252 (DPAK)	2,500/Tape & Reel

Notes:

- 1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information



O':| = Manufacturer's Marking
N4030L = Product Type Marking Code
YYWW = Date Code Marking
YY = Year (ex: 21 = 2021)
WW = Week (01 to 53)



Maximum Ratings (@TA = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit		
Drain-Source Voltage	VDSS	40	V		
Gate-Source Voltage			V _{GSS}	±20	V
Continuous Drain Current (Note 5) V _{GS} = 10V	Steady State	T _A = +25°C T _A = +70°C	ID	9.6 7.7	А
Maximum Body Diode Continuous Current (Note 5)	Is	9.6	Α		
Pulsed Drain Current (10µs Pulse, Duty Cycle = 1%	Ірм	37.7	Α		
Pulsed Source Current (10µs Pulse, Duty Cycle = 1%) (Note 6)			Ism	37.7	Α

Thermal Characteristics (@TA = +25°C, unless otherwise specified.)


Characteristic		Symbol	Value	Unit
Total Power Dissipation (Note 5)	T _A = +25°C	PD	4.18	W
Thermal Resistance, Junction to Ambient (Note 5)	Steady State	Reja	29.9	°C/W
Total Power Dissipation (Note 7)	T _A = +25°C	PD	2.14	W
Thermal Resistance, Junction to Ambient (Note 7)	Steady State	$R_{\theta JA}$	58.4	°C/W
Thermal Resistance, Junction to Case (Note 8)		Rejc	2.46	°C/W
Operating and Storage Temperature Range		TJ, TSTG	-55 to +150	°C

Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)


Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition	
OFF CHARACTERISTICS (Note 9)							
Drain-Source Breakdown Voltage	BVDSS	40		_	V	$V_{GS} = 0V, I_{D} = 250\mu A$	
Zero Gate Voltage Drain Current	IDSS		_	1	μΑ	$V_{DS} = 40V$, $V_{GS} = 0V$	
Gate-Source Leakage	Igss		_	±100	nA	$V_{GS} = \pm 20V$, $V_{DS} = 0V$	
ON CHARACTERISTICS (Note 9)	ON CHARACTERISTICS (Note 9)						
Gate Threshold Voltage	Vgs(TH)	1		3	V	$V_{DS} = V_{GS}$, $I_D = 250\mu A$	
Static Drain-Source On-Resistance	D- avan		21	30	mΩ	V _G S = 10V, I _D = 12A	
Static Diain-Source On-Nesistance	R _{DS(ON)}		37	50	11122	$V_{GS} = 4.5V, I_{D} = 6A$	
Diode Forward Voltage	VsD		0.95	1.1	V	V _{GS} = 0V, I _S = 12A	
DYNAMIC CHARACTERISTICS (Note 10)							
Input Capacitance	Ciss		604	_		V _{DS} = 20V, V _{GS} = 0V, f = 1.0MHz	
Output Capacitance	Coss		106	_	pF		
Reverse Transfer Capacitance	Crss		59.6	_			
Total Gate Charge (VGS = 4.5V)	Qg		6.5	_		Vps = 20V. lp = 12A	
Total Gate Charge (V _{GS} = 10V)	Q_g		12.9	_	nC		
Gate-Source Charge	Qgs		2.3	_	110	VDS = 20V, ID = 12A	
Gate-Drain Charge	Q_{gd}		3.6	_			
Turn-On Delay Time	t _{D(ON)}		4.2	_		$V_{DD} = 20V, I_{D} = 12A$ $V_{GS} = 10V, R_{G} = 6\Omega$	
Turn-On Rise Time	t _R		12.4	_	ns		
Turn-Off Delay Time	tD(OFF)		13.8	_	115		
Turn-Off Fall Time	tF		10.7				
Body Diode Reverse Recovery Time	trr		135	_	ns	IF = 12A, di/dt = 100A/µs	
Body Diode Reverse Recovery Charge	Qrr	_	799	_	nC	IF = 12A, di/dt = 100A/µs	

- Notes: 5. For a device surface mounted on 50mm x 50mm x 1.6mm FR-4 PCB with high coverage of single sided 2oz copper, in still air conditions; the device is measured when operating in a steady-state condition.
 - 6. Same as note 5, except the device is pulsed with D = 0.02 and pulse width 300µs. The pulse current is limited by the maximum junction temperature.
 - 7. For a device surface mounted on 25mm x 25mm x 1.6mm FR-4 PCB with high coverage of single sided 1oz copper, in still air conditions; the device is measured when operating in a steady-state condition.
 - 8. Thermal resistance from junction to solder-point (at the end of the drain lead).
 - 9. Short duration pulse test used to minimize self-heating effect.
 - 10. Guaranteed by design. Not subject to product testing.





















Gate-Source Voltage v Gate Charge



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.




TO252 (DPAK)					
Dim	Min	Max	Тур		
Α	2.19	2.39	2.29		
A1	0.00	0.13	0.08		
A2	0.97	1.17	1.07		
b	0.64	0.88	0.783		
b2	0.76	1.14	0.95		
b3	5.21	5.46	5.33		
С	0.45	0.58	0.531		
D	6.00	6.20	6.10		
D1	5.21	-	-		
е	-	-	2.286		
Е	6.45	6.70	6.58		
E1	4.32	-	-		
Н	9.40	10.41	9.91		
٦	1.40	1.78	1.59		
L3	0.88	1.27	1.08		
L4	0.64	1.02	0.83		
а	0°	10°	-		
All Dimensions in mm					

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

TO252 (DPAK)



Dimensions	Value (in mm)		
С	4.572		
Х	1.060		
X1	5.632		
Y	2.600		
Y1	5.700		
Y2	10.700		



IMPORTANT NOTICE

- 1. DIODES INCORPORATED AND ITS SUBSIDIARIES ("DIODES") MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- 2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes products. Diodes products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of the Diodes products for their intended applications, (c) ensuring their applications, which incorporate Diodes products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- 5. Diodes products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

Copyright © 2021 Diodes Incorporated

www.diodes.com