



#### 300V PNP HIGH VOLTAGE TRANSISTOR IN SOT23

#### **Features**

- BV<sub>CEO</sub> > -300V
- I<sub>C</sub> = -200mA High Continuous Collector Current
- Complementary Type FMMTA42
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- An automotive-compliant part is available under separate datasheet (FMMTA92Q)


#### **Mechanical Data**

- Package: SOT23
- Package Material: Molded Plastic, "Green" Molding Compound UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 (3)
- Weight 0.008 grams (Approximate)










Device Symbol



Top View Pin-Out


#### **Ordering Information** (Note 4)

Orderable	Bookogo	Marking	Reel Size (inches)	Tape Width (mm)	Packing	
Part Number	Package	Marking	Reel Size (Iliches)	Tape Width (mm)	Qty.	Carrier
FMMTA92TA	SOT23	4E	7	8	3,000	Reel

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

#### **Marking Information**



4E = Product Type Marking Code



### Absolute Maximum Ratings (@TA = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Collector-Base Voltage	V <sub>CBO</sub>	-300	V
Collector-Emitter Voltage	V <sub>CEO</sub>	-300	V
Emitter-Base Voltage	$V_{EBO}$	-5	V
Continuous Collector Current	Ic	-200	mA

# Thermal Characteristics (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit		
Power Dissipation	(Note 5)	6	0.31	W	
Power Dissipation	(Note 6)	$P_{D}$	0.35		
Thermal Desistance, Junction to Ambient	(Note 5)	D	403	°C/W	
Thermal Resistance, Junction to Ambient	(Note 6)	$R_{\theta JA}$	357	-C/VV	
Thermal Resistance, Junction to Lead (Note 7)		$R_{ heta JL}$	350	°C/W	
Operating and Storage Temperature Range	$T_{J_i} T_{STG}$	-55 to +150	°C		

### ESD Ratings (Note 8)

Characteristic	Symbol	Value	Unit	JEDEC Class
Electrostatic Discharge - Human Body Model	ESD HBM	4,000	V	3A
Electrostatic Discharge - Machine Model	ESD MM	400	V	С

Notes:

- 5. For a device mounted on minimum recommended pad layout 1oz copper that is on a single-sided 1.6mm FR-4 PCB; device is measured under still air conditions whilst operating in steady state condition.
- Same as note 5, except the device is mounted on 15mm x 15mm 1oz copper.
   Thermal resistance from junction to solder-point (at the end of the collector lead).
   Refer to JEDEC specification JESD22-A114 and JESD22-A115.



### **Thermal Characteristics and Derating Information**




Figure 3. Power Pulse Dissipation

Figure 4. Safe Operating Area



# Electrical Characteristics (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
Collector-Base Breakdown Voltage	$BV_CBO$	-300	_	_	V	$I_{C} = -100 \mu A$
Collector-Emitter Breakdown Voltage (Note 9)	$BV_CEO$	-300	_	_	V	I <sub>C</sub> = -1mA
Emitter-Base Breakdown Voltage	BV <sub>EBO</sub>	-5	_	_	V	I <sub>E</sub> = -100μA
Collector Cutoff Current	I <sub>CES</sub>	_	_	-250	nA	V <sub>CE</sub> = -200V
Collector Cutoff Current	lana		_	-250	nA	V <sub>CB</sub> = -200V
Collector Cutoff Cuttern	I <sub>CBO</sub>	_				V <sub>CB</sub> = -160V
Emitter Cutoff Current	I <sub>EBO</sub>	_	_	-100	nA	$V_{EB} = -3V$
		25	_	_		$I_C = -1mA, V_{CE} = -10V$
Static Forward Current Transfer Ratio (Note 9)	h <sub>FE</sub>	40			_	$I_C = -10 \text{mA}, V_{CE} = -10 \text{V}$
		25	_	_		$I_C = -30 \text{mA}, V_{CE} = -10 \text{V}$
Collector-Emitter Saturation Voltage (Note 9)	V <sub>CE(sat)</sub>	_	_	-0.5	V	$I_C = -20mA, I_B = -2mA$
Base-Emitter Saturation Voltage (Note 9)	V <sub>BE(sat)</sub>	_	_	-0.9	V	$I_C = -20 \text{mA}, I_B = -2 \text{mA}$
Output Capacitance	$C_{ m obo}$	_	_	6	pF	$V_{CB} = -20V$ , $f = 1MHz$
Transition Frequency	f <sub>T</sub>	50	_	_	MHz	$V_{CE} = -20V, I_{C} = -10mA,$ f = 20MHz

Note: 9. Measured under pulsed conditions. Pulse width  $\leq 300 \mu s$ . Duty cycle  $\leq 2\%$ .



# Typical Electrical Characteristics (@T<sub>A</sub> = +25°C, unless otherwise specified.)




Figure 5.  $h_{FE} v I_c$ 





Figure 6. f<sub>T</sub> v I<sub>c</sub>






# **Package Outline Dimensions**

Please see http://www.diodes.com/package-outlines.html for the latest version.

#### SOT23




SOT23					
Dim	Min	Max	Тур		
Α	0.37	0.51	0.40		
В	1.20	1.40	1.30		
С	2.30	2.50	2.40		
D	0.89	1.03	0.915		
F	0.45	0.60	0.535		
G	1.78	2.05	1.83		
Н	2.80	3.00	2.90		
J	0.013	0.10	0.05		
K	0.890	1.00	0.975		
K1	0.903	1.10	1.025		
L	0.45	0.61	0.55		
L1	0.25	0.55	0.40		
М	0.085	0.150	0.110		
а	0°	8°			
All Dimensions in mm					

# **Suggested Pad Layout**

Please see http://www.diodes.com/package-outlines.html for the latest version.

#### SOT23



Dimensions	Value (in mm)
С	2.0
Х	0.8
X1	1.35
Y	0.9
Y1	2.9

Note: For high voltage applications, the appropriate industry sector guidelines should be considered with regards to creepage and clearance distances between device Terminals and PCB tracking.



#### **IMPORTANT NOTICE**

- 1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- 2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- 5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
- 9. This Notice may be periodically updated with the most recent version available at <a href="https://www.diodes.com/about/company/terms-and-conditions/important-notice">https://www.diodes.com/about/company/terms-and-conditions/important-notice</a>

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners.

© 2023 Diodes Incorporated. All Rights Reserved.

www.diodes.com