




40V PNP SMALL SIGNAL TRANSISTOR IN SOT23

Features

- Epitaxial Planar Die Construction
- Ideal for Medium Power Amplification and Switching
- Complementary NPN Type: DIODES MMBT4401
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please <u>contact us</u> or your local Diodes representative. https://www.diodes.com/quality/product-definitions/

Mechanical Data

- Package: SOT23
- Package Material: Molded Plastic "Green" Compound UL Flammability Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 ©3
- Weight: 0.008 grams (Approximate)




Ordering Information (Note 4)

Part Number	Paakaga	Marking	Reel Size (inches)	Tape Width (mm)	Packing	
Fait Number	Package Marking Reel Size (inches)		Reel Size (Illiches)	rape widin (ililii)	Qty.	Carrier
MMBT4403-7-F	SOT23	K2T	7	8	3,000	Reel
MMBT4403-13-F	SOT23	K2T	13	8	10,000	Reel

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information



K2T = Product Type Marking Code YM = Date Code Marking Y = Year (ex: K = 2023) M = Month (ex: 2 = February)

Date Code Kev

Year	2003		2023	2024	2025	2026	2027	2028	2029	2030	2031	2032
Code	Р		K	L	М	N	0	Р	R	S	Т	U
Month	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec



Absolute Maximum Ratings (@TA = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Collector-Base Voltage	Vсво	-40	V
Collector-Emitter Voltage	Vceo	-40	V
Emitter-Base Voltage	VEBO	-6	V
Collector Current - Continuous (Note 7)	Ic	-600	mA

Thermal Characteristics (@TA = +25°C, unless otherwise specified.)

Characteristic		Symbol	Value	Unit	
Collector Rower Discinction	(Note 5)	D-	310	mW	
Collector Power Dissipation	(Note 6)	PD	350	ITIVV	
Thermal Decistores, Junction to Ambient	(Note 5)	D	403	°C/W	
Thermal Resistance, Junction to Ambient	(Note 6)	Reja	357	°C/VV	
Thermal Resistance, Junction to Leads	(Note 7)	R ₀ JL	350	°C/W	
Thermal Resistance, Junction to Case	Rejc	55	°C/W		
Operating and Storage Temperature Range	•	T _J ,T _{STG}	-55 to +150	°C	


Notes:


5. For the device mounted on minimum recommended pad layout FR4 PCB with high coverage of single sided 1oz copper, in still air conditions.


400

- 6. For the device mounted on 15mm x 15mm x 1.6mm FR4 PCB with high coverage of single sided 1oz copper, in still air conditions.
- 7. Thermal resistance from junction to solder-point (at the end of the collector lead).

Thermal Characteristics and Derating Information







Pulse Power Dissipation



Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)


Characteristic	Symbol	Min	Max	Unit	Test Condition	
OFF CHARACTERISTICS (Note 8)						
Collector-Base Breakdown Voltage	BV _{CBO}	-40		V	$I_C = -100 \mu A$	
Collector-Emitter Breakdown Voltage	BVceo	-40		V	Ic = -10mA	
Emitter-Base Breakdown Voltage	BVEBO	-6	_	V	$I_E = -100 \mu A$	
Collector Cutoff Current	ICEX		-100	nA	$V_{CE} = -35V, V_{EB(off)} = -0.4V$	
Base Cutoff Current	I _{BL}	_	-100	nA	$V_{CE} = -35V, V_{EB(off)} = -0.4V$	
ON CHARACTERISTICS (Note 8)						
DC Current Gain	hFE	30 60 100 100 20	 300 		Ic = -100µA, Vce = -1V Ic = -1.0mA, Vce = -1V Ic = -10mA, Vce = -1V Ic = -150mA, Vce = -2V Ic = -500mA, Vce = -2V	
Collector-Emitter Saturation Voltage	VCE(sat)		-0.40 -0.75	V	$I_C = -150 \text{mA}, I_B = -15 \text{mA}$ $I_C = -500 \text{mA}, I_B = -50 \text{mA}$	
Base-Emitter Saturation Voltage	V _{BE(sat)}	-0.75 —	-0.95 -1.30	V	$I_C = -150$ mA, $I_B = -15$ mA $I_C = -500$ mA, $I_B = -50$ mA	
SMALL SIGNAL CHARACTERISTICS						
Output Capacitance	Cobo	_	8.5	pF	$V_{CB} = -10V$, $f = 1.0MHz$, $I_E = 0$	
Input Capacitance	Cibo	_	30	pF	$V_{EB} = -0.5V$, $f = 1.0MHz$, $I_{C} = 0$	
Input Impedance	hie	1.5	15	kΩ		
Voltage Feedback Ratio	h _{re}	0.1	8.0	x 10 ⁻⁴	$V_{CE} = -10V, I_{C} = -1mA,$	
Small Signal Current Gain	h _{fe}	60	500	_	f = 1kHz	
Output Admittance	hoe	1.0	100	μS		
Current Gain-Bandwidth Product	f⊤	200	١	MHz	V _{CE} = -10V, I _C = -20mA, f = 100MHz	
SWITCHING CHARACTERISTICS	SWITCHING CHARACTERISTICS					
Delay Time	td	_	15	ns	Vcc = -30V, Ic = -150mA,	
Rise Time	t _r	_	20	ns	$V_{BE(off)} = -2V$, $I_{B1} = -15mA$	
Storage Time	ts	_	225	ns	Vcc = -30V, Ic = -150mA,	
Fall Time	t _f	<u> </u>	30	ns	$I_{B1} = -I_{B2} = -15mA$	


Note:


8. Short duration pulse test used to minimize self-heating effect.





Typical Electrical Characteristics (@TA = +25°C, unless otherwise specified.)

















Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT23




SOT23						
Dim	Min	Max	Тур			
Α	0.37	0.51	0.40			
В	1.20	1.40	1.30			
C	2.30	2.50	2.40			
D	0.89	1.03	0.915			
F	0.45	0.60	0.535			
G	1.78	2.05	1.83			
Η	2.80	3.00	2.90			
7	0.013	0.10	0.05			
K	0.890	1.00	0.975			
K1	0.903	1.10	1.025			
L	0.45	0.61	0.55			
L1	0.25	0.55	0.40			
М	0.085	0.150	0.110			
а	0°	8°				
All	Dimens	ions in	mm			

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT23



Dimensions	Value (in mm)
С	2.0
Х	0.8
X1	1.35
Υ	0.9
Y1	2.9



IMPORTANT NOTICE

- 1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- 2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- 5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
- 9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners.

© 2023 Diodes Incorporated. All Rights Reserved.

www.diodes.com

MMBT4403 6 of 6 March 2023

Document Number: DS30058 Rev. 13 - 2 www.diodes.com © 2023 Copyright Diodes Incorporated. All Rights Reserved.