

.

Features

- BV_{CEO} > 40V
- I_C = 200mA High Collector Current
- P_D = 1000mW Power Dissipation
- 0.60mm² Package Footprint, 13 Times Smaller than SOT23
- 0.5mm Height Package Minimizing Off-Board Profile
- Complementary PNP Type: MMBT3906LP
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e.: parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please refer to the related automotive grade (Q-suffix) part. A listing can be found at

https://www.diodes.com/products/automotive/automotiveproducts/.

 This part is qualified to JEDEC standards (as references in AEC-Q) for High Reliability. <u>https://www.diodes.com/quality/product-definitions/</u>


Mechanical Data

- Package: X1-DFN1006-3
- Package Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish NiPdAu, Solderable per MIL-STD-202, Method 208 @
- Weight: 0.0008 grams (Approximate)






Bottom View



Device Symbol



Top View Device Schematic

Ordering Information (Note 4)

Orderable Part	Package	Marking	Reel Size (inches)	Tape Width (mm)	Pac	king
Number	Гаскауе	Warking	Reel Size (Inches)	rape width (mm)	Qty.	Carrier
MMBT3904LP-7	X1-DFN1006-3	1N	7	8	3,000	Reel
MMBT3904LP-7B	X1-DFN1006-3	1N	7	8	10,000	Reel

Notes: 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.


2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.



Marking Information





Absolute Maximum Ratings ($@T_A = +25^{\circ}C$, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Collector-Base Voltage	V _{CBO}	60	V
Collector-Emitter Voltage	V _{CEO}	40	V
Emitter-Base Voltage	V _{EBO}	6.0	V
Collector Current	lc	200	mA
Peak Collector Current	I _{CM}	200	mA

Thermal Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit		
Dower Dissipation	(Note 5)	P	400	mW	
Power Dissipation	(Note 6)	- P _D	1000	rrivv	
The sum of Desistences, hunstice to Archiest	(Note 5)	_	310	°C/W	
Thermal Resistance, Junction to Ambient	(Note 6)	R _{0JA}	120		
Thermal Resistance, Junction to Lead (Note 7)		R _{θJL}	120	°C/W	
Operating and Storage and Temperature Ran	T _J , T _{STG}	-55 to +150	°C		

ESD Ratings (Note 8)

Characteristic	Symbol	Value	Unit	JEDEC Class
Electrostatic Discharge - Human Body Model	ESD HBM	4,000	V	3A
Electrostatic Discharge - Machine Model	ESD MM	200	V	В

Notes: 5. For the device mounted on minimum recommended pad layout 2oz copper that is on a single-sided 1.6mm FR4 PCB; device is measured under still air conditions whilst operating in steady state condition.


6. Same as Note 5, except the exposed collector pad is mounted on 25mm x 25mm 2oz copper.

7. Thermal resistance from junction to solder-point (on the exposed collector pad).

8. Refer to JEDEC specification JESD22-A114 and JESD22-A115.



Thermal Characteristics






Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Max	Unit	Test Condition
OFF CHARACTERISTICS					
Collector-Base Breakdown Voltage	ВV _{CBO}	60	_	V	$I_{C} = 10 \mu A, I_{E} = 0 A$
Collector-Emitter Breakdown Voltage (Note 9)	BV _{CEO}	40	_	V	$I_{\rm C} = 1.0 {\rm mA}, I_{\rm B} = 0 {\rm A}$
Emitter-Base Breakdown Voltage	BV _{EBO}	6.0	—	V	$I_{E} = 10 \mu A, I_{C} = 0 A$
Collector Cutoff Current	ICEX		50	nA	$V_{CE} = 30V, V_{EB(off)} = 3.0V$
Base Cutoff Current	I _{BL}	_	50	nA	$V_{CE} = 30V, V_{EB(off)} = 3.0V$
ON CHARACTERISTICS (Note 9)	<u> </u>				•
		40	_		$I_{C} = 100 \mu A, V_{CE} = 1.0 V$
		70	_		I _C = 1.0mA, V _{CE} = 1.0V
DC Current Gain	h _{FE}	100	300	_	$I_{C} = 10 \text{mA}, V_{CE} = 1.0 \text{V}$
		60	_		$I_{C} = 50 \text{mA}, V_{CE} = 1.0 \text{V}$
		30	—		$I_{C} = 100 \text{mA}, V_{CE} = 1.0 \text{V}$
Collector-Emitter Saturation Voltage	N		0.20	V	$I_{C} = 10mA, I_{B} = 1.0mA$
Collector-Emilier Saturation Voltage	V _{CE(sat)}	_	0.30	v	$I_{C} = 50 \text{mA}, I_{B} = 5.0 \text{mA}$
Base-Emitter Saturation Voltage		0.65	0.85	V	$I_{\rm C} = 10 {\rm mA}, I_{\rm B} = 1.0 {\rm mA}$
Base-Elliller Saturation voltage	V _{BE(sat)}		0.95	v	$I_{C} = 50 \text{mA}, I_{B} = 5.0 \text{mA}$
SMALL SIGNAL CHARACTERISTICS					
Output Capacitance	C _{obo}	—	4.0	pF	$V_{CB} = 5.0V$, f = 1.0MHz, I _E = 0A
Input Capacitance	Cibo		8.5	pF	$V_{EB} = 0.5V$, f = 1.0MHz, I _C = 0A
Input Impedance	h _{ie}	1.0	10	kΩ	
Voltage Feedback Ratio	h _{re}	0.5	8.0	x 10 ⁻⁴	$V_{CE} = 10V, I_{C} = 1.0mA$
Small Signal Current Gain	h _{fe}	100	400	—	f = 1.0 kHz
Output Admittance	h _{oe}	1.0	40	μs	
Current Gain-Bandwidth Product	fT	300	_	MHz	$V_{CE} = 20V$, $I_C = 10mA$ f = 100MHz
SWITCHING CHARACTERISTICS					
Delay Time	t _d	_	35	ns	$V_{CC} = 3.0V, I_{C} = 10mA$
Rise Time	tr	—	35	ns	$V_{BE(off)} = 0.5V, I_{B1} = 1.0mA$
Storage Time	ts	—	200	ns	$V_{CC} = 3.0V, I_{C} = 10mA$
Fall Time	t _f	_	50	ns	$I_{B1} = -I_{B2} = 1.0 \text{mA}$

Note: 9. Measured under pulsed conditions. Pulse width \leq 300µs. Duty cycle \leq 2%.




Typical Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)





Package Outline Dimensions


Please see http://www.diodes.com/package-outlines.html for the latest version.



X1-DFN1006-3					
Dim	Min	Max	Тур		
Α	0.47	0.53	0.50		
A1	0.00	0.05	0.03		
b	0.10	0.20	0.15		
b2	0.45	0.55	0.50		
D	0.95	1.075	1.00		
ш	0.55	0.675	0.60		
e	-	-	0.35		
L1	0.20	0.30	0.25		
L2	0.20	0.30	0.25		
L3	-	-	0.40		
Z	0.02	0.08	0.05		
All Dimensions in mm					

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.



Dimensions	Value (in mm)		
С	0.70		
G1	0.30		
G2	0.20		
Х	0.40		
X1	1.10		
Ŷ	0.25		
Y1	0.70		

X1-DFN1006-3



IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

5 Diodes' provided Diodes' Standard Terms and Conditions of Sale products are subject to (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners. © 2023 Diodes Incorporated. All Rights Reserved.

www.diodes.com