

NOT RECOMMENDED FOR NEW DESIGN USE DMC3061SVTQ



DMG6602SVTQ

COMPLEMENTARY PAIR ENHANCEMENT MODE MOSFET

Product Summary

Device	BV _{DSS}	R _{DS} (ON)	I _D T _A = +25°C
Q1	30V	60mΩ @ V _{GS} = 10V	3.4A
Qi	30 V	100mΩ @ V _{GS} = 4.5V	2.7A
Q2	201/	95mΩ @ V _{GS} = -10V	-2.8A
Q2	-30V	140mΩ @ V _{GS} = -4.5V	-2.3A

Features and Benefits

- Low On-Resistance
- Low Input Capacitance
- Fast Switching Speed
- Low Input/Output Leakage
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- The DMG6602SVTQ is suitable for automotive applications requiring specific change control; this part is AEC-Q101 qualified, PPAP capable, and manufactured in IATF 16949 certified facilities.

https://www.diodes.com/quality/product-definitions/


Description and Applications

This new generation MOSFET is designed to minimize the on-state resistance (R_{DS(on)}) yet maintain superior switching performance, making it ideal for high efficiency power management applications.

- Backlighting
- DC-DC converters
- Power management functions

Mechanical Data

- Package: TSOT26
- Package Material: Molded Plastic, "Green" Molding Compound.
 UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals Connections: See Diagram
- Terminals: Finish Matte Tin Annealed over Copper Leadframe. Solderable per MIL-STD-202, Method 208 (3)
- Weight: 0.013 grams (Approximate)



Ordering Information (Note 4)


Part Number	Package	Packing			
Fait Williber	rackage	Qty.	Carrier		
DMG6602SVTQ-7	TSOT26	3,000	Tape & Reel		
DMG6602SVTQ-13	TSOT26	10,000	Tape & Reel		

Notes: 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.

- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/



Marking Information



66C = Product Type Marking Code YM = Date Code Marking Y = Year (ex: J = 2022) M = Month (ex: 1 = January)

Date Code Key

Year	2014		2022	2023	2024	2025	2026	2027	2028	2029	2030	2031
Code	В		7	K	L	М	N	0	P	R	S	Т
	-	-				-						

Month	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec
Code	1	2	3	4	5	6	7	8	9	0	N	D

Maximum Ratings - Q1 (@T_A = +25°C unless otherwise specified.)

Characteristi	С		Symbol	Value	Unit
Drain-Source Voltage			V _{DSS}	30	V
Gate-Source Voltage			Vgss	±20	V
Continuous Drain Current (Note 6) V _{GS} = 10V	Steady State	T _A = +25°C T _A = +70°C	I _D	3.4 2.7	А
Continuous Drain Current (Note 6) V _{GS} = 4.5V	Steady State	T _A = +25°C T _A = +70°C	lD	2.7 2.2	А
Maximum Continuous Body Diode Forward Current	(Note 6)		Is	1.5	А
Pulsed Drain Current (Note 6)			IDM	25	Α

Maximum Ratings - Q2 (@TA = +25°C unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Drain-Source Voltage	V_{DSS}	-30	V
Gate-Source Voltage	Vgss	±20	V
Continuous Drain Current (Note 6) Vgs = -10V Steady $T_A = +25^{\circ}C$ $T_A = +70^{\circ}C$	ID	-2.8 -2.4	А
Continuous Drain Current (Note 6) $V_{GS} = -4.5V$ Steady $T_A = +25^{\circ}C$ $T_A = +70^{\circ}C$	ID	-2.3 -2.1	А
Maximum Continuous Body Diode Forward Current (Note 6)	Is	-1.5	Α
Pulsed Drain Current (Note 6)	lD	-20	A

Thermal Characteristics

Characteristic		Symbol	Value	Units	
Total Power Dissipation (Note 5)	T _A = +25°C	D-	0.84	W	
Total Power Dissipation (Note 9)	$T_A = +70^{\circ}C$	P _D	0.52		
Thermal Resistance, Junction to Ambient (Note 5)	Steady State	D	155	°C/W	
Thermal Resistance, Junction to Ambient (Note 3)	t<10s	$R_{\theta JA}$	109		
Total Power Dissipation (Note 6)	$T_A = +25$ °C	D-	1.27	W	
Total Fower Dissipation (Note 6)	$T_A = +70$ °C	PD	0.8		
Thermal Resistance, Junction to Ambient (Note 6)	Steady State	D	102		
Thermal Resistance, Junction to Ambient (Note 6)	t<10s	R _θ JA	71	°C/W	
Thermal Resistance, Junction to Case (Note 6)		R _θ JC	34		
Operating and Storage Temperature Range		TJ, TSTG	-55 to +150	°C	

Notes: 5. Device mounted on FR-4 substrate PC board, 2oz copper, with minimum recommended pad layout.

^{6.} Device mounted on FR-4 substrate PC board, 2oz copper, with 1inch square copper plate.



Electrical Characteristics – Q1 NMOS (@ T_A = +25°C unless otherwise stated.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
OFF CHARACTERISTICS (Note 7)		1	7.	ı		,
Drain-Source Breakdown Voltage	BVDSS	30	_	_	V	V _G S = 0V, I _D = 250µA
Zero Gate Voltage Drain Current	IDSS	_		1.0	μΑ	V _{DS} = 24V, V _{GS} = 0V
Gate-Source Leakage	I _{GSS}	_		±100	nA	$V_{GS} = \pm 20V, V_{DS} = 0V$
ON CHARACTERISTICS (Note 7)						
Gate Threshold Voltage	V _{GS(TH)}	1.0	_	2.3	V	$V_{DS} = V_{GS}$, $I_D = 250\mu A$
Static Drain-Source On-Resistance	Process		38	60	mΩ	$V_{GS} = 10V, I_{D} = 3.1A$
Static Drain-Source On-Nesistance	RDS(ON)		55	100	11122	$V_{GS} = 4.5V$, $I_{D} = 2A$
Forward Transfer Admittance	Y _{fs}	_	4	_	S	$V_{DS} = 5V, I_{D} = 3.1A$
Diode Forward Voltage	VsD		0.8	1	V	$V_{GS} = 0V$, $I_{S} = 1A$
DYNAMIC CHARACTERISTICS (Note 8)						
Input Capacitance	Ciss	_	290	400	Y	
Output Capacitance	Coss		40	80	pF	$V_{DS} = 15V, V_{GS} = 0V, f = 1.2MHz$
Reverse Transfer Capacitance	Crss	_	40	80		
Gate Resistance	R_g	_	1.4	+	Ω	$V_{DS} = 0V$, $V_{GS} = 0V$, $f = 1MHz$
Total Gate Charge (V _{GS} = 4.5V)	Qg		4	6		$V_{DS} = 15V$, $V_{GS} = 4.5V$, $I_{D} = 3.1A$
Total Gate Charge (Vgs = 10V)	Qg	_	9	13	nC	
Gate-Source Charge	Qgs		1.2		110	$V_{DS} = 15V$, $V_{GS} = 10V$, $I_{D} = 3A$
Gate-Drain Charge	Q_{gd}		1.5			
Turn-On Delay Time	t _{D(on)}	1	3	_		
Turn-On Rise Time	t _r		5	_	nc	$V_{GS} = 10V, V_{DS} = 15V,$
Turn-Off Delay Time	tD(off)		13		ns	$R_G = 3\Omega$, $R_L = 4.7\Omega$
Turn-Off Fall Time	tf		3			

Electrical Characteristics – Q2 PMOS (@ T_A = +25°C unless otherwise stated.)


				7			
Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition	
OFF CHARACTERISTICS (Note 7)			_				
Drain-Source Breakdown Voltage	BVDSS	-30	_	_	V	$V_{GS} = 0V, I_{D} = -250\mu A$	
Zero Gate Voltage Drain Current	IDSS	_	_	-1.0	μΑ	$V_{DS} = -24V, V_{GS} = 0V$	
Gate-Source Leakage	Igss	1	_	±100	nA	$V_{GS} = \pm 20V$, $V_{DS} = 0V$	
ON CHARACTERISTICS (Note 7)							
Gate Threshold Voltage	VGS(TH)	-1.0	_	-2.3	٧	$V_{DS} = V_{GS}$, $I_D = -250\mu A$	
Static Drain-Source On-Resistance	Process		73	95	mΩ	$V_{GS} = -10V, I_{D} = -2.7A$	
Static Drain-Source On-Resistance	R _{DS} (ON)	_	99	140	11122	$V_{GS} = -4.5V, I_{D} = -2A$	
Forward Transfer Admittance	Y _{fs}	_	6	_	S	$V_{DS} = -5V$, $I_{D} = -2.7A$	
Diode Forward Voltage	V _{SD}	_	-0.8	-1.0	V	Vgs = 0V, Is = -1A	
DYNAMIC CHARACTERISTICS (Note 8)							
Input Capacitance	Ciss	_	350	420		45)/)/ 0)/	
Output Capacitance	Coss	_	50	100	pF	V _{DS} = -15V, V _{GS} = 0V, f = 1.2MHz	
Reverse Transfer Capacitance	Crss	_	45	80		1 - 1.21/11 12	
Gate Resistance	Rg	_	17.1	_	Ω	$V_{DS} = 0V$, $V_{GS} = 0V$, $f = 1MHz$	
Total Gate Charge (Vgs = -4.5V)	Qg	_	4	6		$V_{DS} = -15V$, $V_{GS} = -4.5V$, $I_{D} = -3A$	
Total Gate Charge (V _{GS} = -10V)	Qg	_	7	9	nC		
Gate-Source Charge	Qgs	_	0.9	_	iiC	$V_{DS} = -15V$, $V_{GS} = -10V$, $I_{D} = -3A$	
Gate-Drain Charge	Qgd	_	1.2	_			
Turn-On Delay Time	t _{D(on)}	_	4.8	_			
Turn-On Rise Time	tr	_	7.3	_	ns	Vgs = -10V, Vps = -15V,	
Turn-Off Delay Time	t _{D(off)}	_	20	_	115	$R_G = 6\Omega$, $R_L = 15\Omega$	
Turn-Off Fall Time	tf	_	13				

Notes:

- 7. Short duration pulse test used to minimize self-heating effect.
- 8. Guaranteed by design. Not subject to production testing.



Q1 NMOS








Fig. 7 Gate Threshold Variation vs. Ambient Temperature






Fig. 9 Typical Junction Capacitance


Fig. 11 SOA, Safe Operation Area







Q2 PMOS












Fig. 18 Gate Threshold Variation vs. Ambient Temperature

















Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

TSOT26




	TSOT26								
Dim	Min	Max	Тур						
Α	-	1.00	_						
A1	0.010	0.100	-						
A2	0.840	0.900	-						
D	2.800	3.000	2.900						
E	2	.800 BS	С						
E1	1.500	1.700	1.600						
b	0.300	0.450	-						
С	0.120	0.200	-						
е	0	.950 BS	С						
e1	1	.900 BS	S						
L	0.30	0.50	_						
▶ L2		.250 BS	_						
θ	0°	8°	4°						
θ1	4°	12°	-						
Δ	All Dimensions in mm								

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

TSOT26



Dimensions	Value (in mm)
С	0.950
Х	0.700
Y	1.000
V1	3 200



IMPORTANT NOTICE

- 1. DIODES INCORPORATED AND ITS SUBSIDIARIES ("DIODES") MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- 2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes products. Diodes products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of the Diodes products for their intended applications, (c) ensuring their applications, which incorporate Diodes products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- 5. Diodes products are provided subject to Diodes Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

Copyright © 2022 Diodes Incorporated

www.diodes.com