



P-CHANNEL ENHANCEMENT MODE MOSFET

Product Summary

BV _{DSS}	Rds(on) max	ID MAX TA = +25°C	
-60V	$55m\Omega$ @ V _{GS} = -10V	-10.4A	
-60 V	$80m\Omega$ @ V _{GS} = -4.5V	-9.2A	

Description and Applications

This MOSFET is designed to meet the stringent requirements of automotive applications. It is qualified to AEC-Q101, supported by a PPAP and is ideal for use in:

- Disconnect Switches
- Motor Control

Features and Benefits

- 100% Unclamped Inductive Switch (UIS) Test in Production
- Low On-Resistance
- Fast Switching Speed
- Low Threshold
- Low Gate Drive
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e.: parts qualified to AEC-Q100/101/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please refer to the related automotive grade (Q-suffix) part. A listing can be found at

https://www.diodes.com/products/automotive/automotive-products/.

 This part is qualified to JEDEC standards (as references in AEC-Q) for High Reliability.

https://www.diodes.com/quality/product-definitions/


Mechanical Data


- Case: TO252
- Case Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminal Connections: See Diagram
- Terminals: Finish Matte Tin Finish Annealed over Copper Leadframe. Solderable per MIL-STD-202, Method 208 ⁽³⁾
- Weight: 0.33 grams (Approximate)

TO252 (DPAK)



Top View





Equivalent Circuit

Ordering Information (Note 4)


Part Number	Case	Packaging
ZXMP6A18KTC	TO252 (DPAK)	2,500/Tape & Reel

Notes:

- 1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/



Marking Information



ZXMP6A18 = Product Type Marking Code YYWW = Date Code Marking YY = Year (ex: 20 = 2020)WW = Week (01 to 53)

Maximum Ratings (@TA = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit		
Drain-Source Voltage		VDSS	-60	V	
Gate-Source Voltage		Vgss	±20	V	
	T _A = +25°C (Note 6)		-10.4	А	
Continuous Drain Current, VGS = -10V	$T_A = +70^{\circ}C \text{ (Note 6)}$	ID	-8.3		
	T _A = +25°C (Note 5)		-6.8		
Pulsed Drain Current (10µs Pulse, Duty Cycle = 1%) (Not	I _{DM}	-37.5	А		
Maximum Body Diode Forward Current (Note 6)		ls	-10.4	Α	
Pulsed Source Current (10µs Pulse, Duty Cycle = 1%) (Note 7)		lsм	-37.5	Α	
Avalanche Current, L = 0.1mH		las	-36	Α	
Avalanche Energy, L = 0.1mH		Eas	65	mJ	

Thermal Characteristics (@ T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit	
Total Power Dissipation (Note 5)		PD	4.3	W
Thermal Resistance, Junction to Ambient (Note 5)	Steady State	RθJA	29	°C/W
Total Power Dissipation (Note 6)		P _D	10.1	W
Thermal Resistance, Junction to Ambient (Note 6)	Steady State	$R_{\theta JA}$	12.3	°C/W
Total Power Dissipation (Note 8)		PD	2.15	W
Thermal Resistance, Junction to Case (Note 8)	Steady State	RθJA	58	°C/W
Operating and Storage Temperature Range		$T_{J_i}T_{STG}$	-55 to +150	°C

5. For a device surface mounted on 50mm x 50mm x 1.6mm FR-4 PCB with high coverage of single sided 2oz copper, in still air conditions. Notes:

- For a device surface mounted on FR-4 PCB measured at t <=10s.
 Repetitive rating 50mm x 50mm x 1.6mm FR-4 PCB, D=0.02 pulse width=300s pulse width limited by maximum junction temperature.
 For a device surface mounted on 25mm x 25mm x 1.6mm FR-4 PCB with high coverage of single sided 1oz copper, in still air conditions.




Electrical Characteristics (@ T_A = +25°C, unless otherwise specified.)


Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition	
OFF CHARACTERISTICS (Note 9)							
Drain-Source Breakdown Voltage	BV _{DSS}	-60		_	V	$V_{GS} = 0V, I_{D} = -250\mu A$	
Zero Gate Voltage Drain Current	IDSS		_	-1	μΑ	$V_{DS} = -60V, V_{GS} = 0V$	
Gate-Source Leakage	I _{GSS}	_	_	±100	nA	$V_{GS} = \pm 20V, V_{DS} = 0V$	
ON CHARACTERISTICS (Note 9)							
Gate Threshold Voltage	Vgs(TH)	-1.0	_	_	V	$V_{DS} = V_{GS}$, $I_D = -250\mu A$	
Static Drain-Source On-Resistance	Dagger		– 44 55 mΩ	$V_{GS} = -10V, I_{D} = -3.5A$			
Static Dialit-Source Off-Resistance	RDS(ON)		59	80	1112.2	$V_{GS} = -4.5V, I_{D} = -2.9A$	
Forward Transconductance	g _{fs}	_	8.7	_	S	$V_{DS} = -15V, I_{D} = -3.5A$	
Diode Forward Voltage	VsD	_	-0.85	-0.95	V	Vgs = 0V, Is = -4.2A	
DYNAMIC CHARACTERISTICS (Note 10)							
Input Capacitance	Ciss	_	1580	_		$V_{DS} = -30V$, $V_{GS} = 0V$ f = 1MHz	
Output Capacitance	Coss		160	_	pF		
Reverse Transfer Capacitance	Crss		140	_			
Total Gate Charge (V _{GS} = -5V)	QG		23	_		V _{DS} = -30V, I _D = -3.5A	
Total Gate Charge (V _{GS} = -10V)	Q _G	_	44	_	nC		
Gate-Source Charge	Q _{GS}		3.9	_	nc		
Gate-Drain Charge	Q _{GD}	_	9.8	_			
Turn-On Delay Time	t _{D(ON)}		4.6	_		V _G S = -10V, V _{DD} = -30V,	
Turn-On Rise Time	t _R		5.8	_			
Turn-Off Delay Time	tD(OFF)		55	_	ns	$R_g = 6\Omega$, $I_D = -1A$	
Turn-Off Fall Time	tF		23	_			
Reverse Recovery Time	trr		37	_	ns	Is = -2.1A, di/dt = -100A/µs	
Reverse Recovery Charge	Q _{RR}		56	_	nC	I _S = -2.1A, di/dt = -100A/µs	

Notes: 9. Short duration pulse test used to minimize self-heating effect.


^{10.} Guaranteed by design. Not subject to product testing.














Typical Transfer Characteristics




Normalised Curves v Temperature






Source-Drain Diode Forward Voltage




Capacitance v Drain-Source Voltage




Gate-Source Voltage v Gate Charge







Basic gate charge waveform



Gate charge test circuit



Switching time waveforms




Switching time test circuit



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

TO252 (DPAK)




TO252 (DPAK)					
Dim	Min	Max	Тур		
Α	2.19	2.39	2.29		
A1	0.00	0.13	0.08		
A2	0.97	1.17	1.07		
b	0.64	0.88	0.783		
b2	0.76	1.14	0.95		
b3	5.21	5.46	5.33		
С	0.45	0.58	0.531		
D	6.00	6.20	6.10		
D1	5.21	-	-		
е	-	-	2.286		
Е	6.45	6.70	6.58		
E1	4.32	-	-		
Н	9.40	10.41	9.91		
L	1.40	1.78	1.59		
L3	0.88	1.27	1.08		
L4	0.64	1.02	0.83		
а	0°	10°	-		
All Dimensions in mm					

Suggested Pad Layout

 $\label{please} Please see \ http://www.diodes.com/package-outlines.html \ for the \ latest \ version.$

TO252 (DPAK)



Dimensions	Value (in mm)			
С	4.572			
Х	1.060			
X1	5.632			
Υ	2.600			
Y1	5.700			
Y2	10.700			



IMPORTANT NOTICE

- 1. DIODES INCORPORATED AND ITS SUBSIDIARIES ("DIODES") MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- 2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes products. Diodes products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of the Diodes products for their intended applications, (c) ensuring their applications, which incorporate Diodes products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- 5. Diodes products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

Copyright © 2020 Diodes Incorporated

www.diodes.com