

2DB1713

12V PNP MEDIUM POWER TRANSISTOR IN SOT89

Features


- BVcEo > -12V
- Ic = -3A High Continuous Current
- Low Saturation Voltage V_{CE(sat)} < -0.25V @ -1.5A
- Complementary NPN Type: 2DD2678
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please <u>contact us</u> or your local Diodes representative. https://www.diodes.com/quality/product-definitions/

Mechanical Data

- Package: SOT89
- Package Material: Molded Plastic, "Green" Molding Compound.
 UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 (2)
- Weight: 0.052 grams (Approximate)

Application

- Medium power switching
- Amplifications




Ordering Information (Note 4)

Part Number	Pookogo	Package Marking Reel Size (inche		Tape Width (mm)	Packing	
Part Number	Package	Warking	Reel Size (Iliches)	Tape Width (IIIII)	Qty.	Carrier
2DB1713-13	SOT89	1713	13	12	2500	Reel

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information



1713 = Product Type Marking Code YWW = Date Code Marking Y or \overline{Y} = Last Digit of Year (ex: 3 = 2023) WW = Week Code (01 to 53)



Absolute Maximum Ratings ($@T_A = +25^{\circ}C$, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Collector-Base Voltage	Vсво	-15	V
Collector-Emitter Voltage	Vceo	-12	V
Emitter-Base Voltage	VEBO	-6	V
Continuous Collector Current	lc	-3	А
Peak Pulse Current	Ісм	-6	A

Thermal Characteristics (@TA = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Power Dissipation (Note 5)	PD	0.9	W
Thermal Resistance, Junction to Ambient Air (Note 5)	R _θ JA	139	°C/W
Power Dissipation (Note 6)	PD	2	W
Thermal Resistance, Junction to Ambient Air (Note 6)	$R_{ heta JA}$	62.5	°C/W
Operating and Storage Temperature Range	TJ, TSTG	-55 to +150	°C

Notes:

- 5. Device mounted on FR-4 PCB with minimum recommended pad layout.
- 6. Device mounted on FR-4 PCB with 1inch² copper pad layout.

Thermal Characteristics and Derating Information




Figure 1. Power Dissipation vs. Ambient Temperature




Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Conditions
OFF CHARACTERISTICS (Note 7)						
Collector-Base Breakdown Voltage	ВУсво	-15		_	V	$I_C = -10\mu A$
Collector-Emitter Breakdown Voltage	BVceo	-12	_	_	V	Ic = -1mA
Emitter-Base Breakdown Voltage	BV_{EBO}	-6	_	_	V	$I_E = -10\mu A$
Collector Cut-Off Current	Ісво	_	_	-0.1	μΑ	V _{CB} = -15V
Emitter Cut-Off Current	I _{EBO}	_	_	-0.1	μΑ	V _{EB} = -6V
ON CHARACTERISTICS (Note 7)						
Collector-Emitter Saturation Voltage	VcE(sat)	_	-120	-250	mV	$I_C = -1.5A$, $I_B = -30mA$
DC Current Gain	h _{FE}	270	_	680	_	$V_{CE} = -2V, I_{C} = -500mA$
SMALL SIGNAL CHARACTERISTICS						
Output Capacitance	Cobo	_	40	_	pF	$V_{CB} = -10V$, $I_{E} = 0$, $f = 1MHz$
Current Gain-Bandwidth Product	fτ	_	180	_	MHz	V _{CE} = -2V, I _C = -100mA, f = 100MHz

Note: 7. Measured under pulsed conditions. Pulse width ≤ 300µs. Duty cycle ≤ 2%.

Typical Electrical Characteristics (@TA = +25°C, unless otherwise specified.)






Figure 4. Typical Collector-Emitter Saturation Voltage vs. Collector Current




Figure 3. Typical DC Current Gain vs. Collector Current




Figure 5. Typical Base-Emitter Turn-On Voltage vs. Collector Current



Typical Electrical Characteristics (@TA = +25°C, unless otherwise specified.) (continued)




Figure 6. Typical Base-Emitter Saturation Voltage vs. Collector Current




Figure 8. Typical Gain-Bandwidth Product vs. Collector Current





Figure 7. Typical Capacitance Characteristics



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT89




SOT89					
Dim	Min	Max	Тур		
Α	1.40	1.60	1.50		
В	0.50	0.62	0.56		
B1	0.42	0.54	0.48		
С	0.35	0.43	0.38		
D	4.40	4.60	4.50		
D1	1.62	1.83	1.733		
D2	1.61	1.81	1.71		
Е	2.40	2.60	2.50		
E2	2.05	2.35	2.20		
е	1	-	1.50		
Н	3.95	4.25	4.10		
H1	2.63	2.93	2.78		
L	0.90	1.20	1.05		
L1	0.327	0.527	0.427		
z	0.20	0.40	0.30		
All Dimensions in mm					

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT89



value		
(in mm)		
1.500		
0.244		
0.580		
0.760		
1.933		
1.730		
3.030		
1.500		
0.770		
4.530		



IMPORTANT NOTICE

- DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and
- Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- Diodes' provided Diodes' Standard Terms and Conditions of Sale products subject to (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing. Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
- 9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-andconditions/important-notice

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners. © 2023 Diodes Incorporated. All Rights Reserved.

www.diodes.com

6 of 6 2DB1713 June 2023 © 2023 Copyright Diodes Incorporated. All Rights Reserved. www.diodes.com