


Features

- BVCEO > -20V
- I_C = -2A Continuous Collector Current
- I_{CM} = -4A Peak Pulse Current
- Low Saturation Voltage V_{CE(sat)} < -120mV @ -1A
- R_{CE(sat)} = 40mΩ for A Low Equivalent On-Resistance
- Complimentary NPN Type : DIODES[™] DSS20201L
- Totally Lead-Free & Fully RoHS compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please <u>contact us</u> or your local Diodes representative. <u>https://www.diodes.com/quality/product-definitions/</u>

Mechanical Data

- Package: SOT23
- Package Material: Molded Plastic, "Green" Molding Compound UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 (3)
- Weight: 0.008 grams (Approximate)



Ordering Information (Note 4)

Part Number	Package Marking Code Reel Size (Inches) Tape Width (mm)		Pac	king		
Fait Nulliper	Fackage	warking code	Reel Size (inches)	Tape width (mm)	Qty.	Carrier
DSS20200L-7	SOT23	ZP1	7	8	3,000	Reel
DSS20200L-13	SOT23	ZP1	13	8	10,000	Reel


Notes: 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.

2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information



ZP1 = Product Type Marking Code YM = Date Code Marking Y = Year (ex: K = 2023) M = Month (ex: 9 = September)

Date Code Key

	1											
Year	2008		2023	2024	2025	2026	2027	2028	2029	2030	2031	2032
Code	V		К	L	М	Ν	0	Р	R	S	Т	U
											-	-
							-			_		
Month	Jan	Feb	Mar	Apr	Мау	Jun	Jul	Aug	Sep	Oct	Nov	Dec



Absolute Maximum Ratings (@TA = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Collector-Base Voltage	V _{CBO}	-20	V
Collector-Emitter Voltage	VCEO	-20	V
Emitter-Base Voltage	VEBO	-7	V
Peak Pulse Collector Current	Ісм	-4	A
Continuous Collector Current	lc	-2	A

Thermal Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic		Symbol	Value	Unit	
Dower Dissinction	(Note 5)	D	600	m)//	
Power Dissipation	(Note 6)	PD	1200	mW	
Thermal Desistance, Junction to Ambient Air	(Note 5)	P	209		
Thermal Resistance, Junction to Ambient Air	(Note 6)	Reja	104	°C/W	
Thermal Resistance, Junction to Leads	(Note 7)	Rejl	75		
Operating and Storage Temperature Range		T _J , T _{STG}	-55 to +150	°C	


ESD Ratings (Note 8)

Characteristic	Symbol	Value	Unit	JEDEC Class
Electrostatic Discharge - Human Body Model	ESD HBM	4,000	V	3A
Electrostatic Discharge - Machine Model	ESD MM	400	V	С

Notes: 5. For a device mounted on minimum recommended pad layout with 1oz copper that is on a single-sided 1.6mm FR4 PCB; device is measured under still b) a device monted on minimum recommended paragout with 102 copper air conditions whilst operating in a steady-state.
c) Same as note (5), except mounted on 25mm x 25mm 1oz copper.
Thermal resistance from junction to solder-point (at the end of collector lead).
Refer to JEDEC specification JESD22-A114 and JESD22-A115.



Thermal Characteristics and Derating Information





Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Conditions
OFF CHARACTERISTICS						
Collector-Base Breakdown Voltage	BV _{CBO}	-20	_		V	I _C = -100μA
Collector-Emitter Breakdown Voltage (Note 9)	BVCEO	-20	_		V	Ic = -10mA
Emitter-Base Breakdown Voltage	BVEBO	-7	_		V	I _E = -100μA
Collector-Base Cutoff Current	I _{CBO}	_		-100	nA	$V_{CB} = -20V, I_E = 0$
Emitter-Base Cutoff Current	IEBO	_		-100	nA	V _{EB} = -7V, I _C = 0
ON CHARACTERISTICS (Note 9)				•	•	
		250	_	_		$V_{CE} = -2V, I_{C} = -10mA$
DC Current Gain	h	250	_]	$V_{CE} = -2V, I_C = -500mA$
	hfe	180	_] —	Vce = -2V, Ic = -1A
		150	_	_		Vce = -2V, Ic = -2A
		_	_	-13		Ic = -0.1A, I _B = -10mA
Collector Emitter Seturation Voltage	N	_	-50	-90	mV	I _C = -1A, I _B = -100mA
Collector-Emitter Saturation Voltage	V _{CE(sat)}	_	-100	-120		Ic = -1A, I _B = -10mA
		_	-80	-180		Ic = -2A, I _B = -200mA
Equivalent On-Resistance	RCE(sat)	_	40	90	mΩ	Ic = -2A, I _B = -200mA
Base-Emitter Saturation Voltage	V _{BE(sat)}	_	_	-0.9	V	I _C = -1A, I _B = -10mA
Base-Emitter Turn-on Voltage	VBE(on)	_	_	-0.9	V	Vce = -2V, Ic = -1A
SMALL SIGNAL CHARACTERISTICS				•	•	
Transition Frequency	fT	100		_	MHz	$V_{CE} = -5V, I_C = -100mA, f = 100MHz$
Output Capacitance	C _{obo}	_	_	100	pF	V _{CB} = -3V, f = 1MHz
Input Capacitance	Cibo	_	_	330	pF	V _{EB} = -0.5V, f = 1MHz
SWITCHING CHARACTERISTICS				•	•	
Turn-On Time	ton	_	_	180	ns	
Delay Time	td	_	_	60	ns	Vcc = -15V, lc = -750mA, I _{B1} = -15mA
Rise Time	tr	_		120	ns	
Turn-Off Time	toff	_		430	ns	
Storage Time	ts	_		300	ns	Vcc = -15V, lc = -750mA, I _{B1} = -I _{B2} = -15mA
Fall Time	t _f	_	_	130	ns	$-1B_1 = -1B_2 = -15111A$

Note: 9. Measured under pulsed conditions. Pulse width \leq 300µs. Duty cycle \leq 2%.



1,000 2.0 $-T_{A} = 150^{\circ}C$ 1.8 -Ic, COLLECTOR CURRENT (A) $T_A = 85^{\circ}C$ +++++ 1.6 $T_A = 25^{\circ}C$ I_B = -5mA hFE, DC CURRENT GAIN 1.4 = -4mA 1.2 $T_A = -55^{\circ}C$ | | |||| 100 1.0 I_B = -3mA 0.8 $I_B = -2mA$ 0.6 $V_{CE} = -2V$ 0.4 $I_B = -1mA$ 0.2 0 10 0.1 1 10 100 1.000 -I_C, COLLECTOR CURRENT (mA) 10.000 10 8 2 6 0 4 -V_{CE,} COLLECTOR EMITTER VOLTAGE (V) Figure 5. $h_{FE} v I_C$ Figure 4. I_C v V_{CE} 1.2 1 $I_{\rm C}/I_{\rm B} = 10$ -2V VCE 1.0 0.1 0.8 T_A = 150°C -V_{CE(sat)}, (V) T_A = -55°C -V_{BE(on)}, (V) $T_A = 85^{\circ}C$ 0.6 T_A = 25°C = 25°C 0.01 0.4 $T_A = 85^{\circ}C$ $T_A = -55^{\circ}C$ +++ $T_A = 150^{\circ}C$ 0.2 0.001 0 10 100 1.000 -I_c, COLLECTOR CURRENT (mA) 10 100 1,000 -I_C, COLLECTOR CURRENT (mA) 10.000 10,000 Figure 7. V_{BE(on)} v I_C Figure 6. $V_{CE(sat)} v I_C$ 1.2 1,000 $I_{\rm C}/I_{\rm B} = 10$ 1MHz 1.0 CAPACITANCE (pF) 0.8 100 $T_A = -55^{\circ}C$ C_{ibo} -V_{BE(sat)}, (V) 0.6 T_A = 25℃ $T_A = 85^{\circ}C$ 0.4 10 $T_A = 150^{\circ}C$ 0.2 0 1 1 100 1.000 10.000 10 0.1 100 10

Typical Electrical Characteristics (@TA = +25°C, unless otherwise specified.)

DSS20200L Document number: DS31604 Rev. 4 - 2

-Ic, COLLECTOR CURRENT (mA)


Figure 8. $V_{BE(sat)} v I_C$

5 of 8 www.diodes.com V_{R,} REVERSE VOLTAGE (V)

Figure 9. Capacitance v V_R




Typical Electrical Characteristics (@TA = +25°C, unless otherwise specified. continued)





Package Outline Dimensions


Please see http://www.diodes.com/package-outlines.html for the latest version.



SOT23						
Dim	Min	Max	Тур			
Α	0.37	0.51	0.40			
В	1.20	1.40	1.30			
С	2.30	2.50	2.40			
D	0.89	1.03	0.915			
F	0.45	0.60	0.535			
G	1.78	2.05	1.83			
Н	2.80	3.00	2.90			
J	0.013	0.10	0.05			
K	0.890	1.00	0.975			
K1	0.903	1.10	1.025			
L	0.45	0.61	0.55			
L1	0.25	0.55	0.40			
М	0.085	0.150	0.110			
а	0°	8°				
All	Dimens	ions in	mm			

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.



SOT23

Dimensions	Value (in mm)
С	2.0
Х	0.8
X1	1.35
Y	0.9
Y1	2.9

Document number: DS31604 Rev. 4 - 2

DSS20200L



IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

5 Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. DIODES is a trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners. © 2023 Diodes Incorporated. All Rights Reserved.

www.diodes.com