X2-DFN1010-6



CONFIGURABLE MULTIPLE-FUNCTION GATE


Description

The 74LVC1G98 is a single 3-input positive configurable multiple function gate with a standard push-pull output. The output state is determined by eight patterns of 3-bit input. The user can chose the logic functions MUX, AND, OR, NAND, NOR, inverter or non-inverting buffer. All inputs can be connected to ground or V_{CC} as required. The device is designed for operation with a power supply range of 1.65V to 5.5V. The inputs are tolerant to 5.5V allowing this device to be used in a mixed voltage environment. The device is fully specified for partial power down applications using IOFF. The IOFF circuitry disables the output preventing damaging current backflow when the device is powered down. The user is reminded that the device can simulate several types of logic gates but may respond differently due to the Schmitt action at the inputs.

Features

- Wide Supply Voltage Range from 1.65V to 5.5V
- ± 24mA Output Drive at 3.3V
- CMOS low power consumption
- IOFF Supports Partial-Power-Down Mode Operation
- Inputs accept up to 5.5V
- ESD Protection Exceeds JESD 22
 - 200-V Machine Model (A115-A)
 - 2000-V Human Body Model (A114-A)
- Latch-Up Exceeds 100mA per JESD 78, Class II
- Range of Package Options
- SOT26, SOT363, DFN1410, and DFN1010: Available in "Green" Molding Compound (no Br, Sb)
 - Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
 - Halogen and Antimony Free. "Green" Device (Note 3)

Pin Assignments



Applications

- Voltage Level Shifting
- General Purpose Logic
- Power Down Signal Isolation

X2-DFN1410-6

- Wide array of products such as:
 - PCs, networking, notebooks, netbooks, PDAs
 - Computer peripherals, hard drives, CD/DVD ROM
 - TV, DVD, DVR, set top box
 - Cell Phones, Personal Navigation / GPS
 - MP3 players ,Cameras, Video Recorders

Notes:


- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant.
- 2. See http://www.diodes.com for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.



Pin Descriptions

Pin Name	Function
IN1	Data Input
GND	Ground
IN0	Data Input
Υ	Data Output
Vcc	Supply Voltage
IN2	Data Input

Logic Diagram




Function Table


	Inputs		Output
IN2	IN1	Υ	
L	لــ	L	Н
L	┙	Н	H
L	Н	L	L
L	Н	Н	لــ
Н	L	L	Н
Н	L	Н	L
Н	Н	L	Н
Н	Н	Н	L




Logic Configurations




Configuration 1
2 to 1 Data Selector with Inverted Output




Configuration 2 2-Input NAND Gate 2-Input OR Gate with Both Inputs Inverted




Configuration 3
2-Input NAND Gate with B Input Inverted
2-Input OR Gate with A Input Inverted



Configuration 4
2-Input OR Gate with One Input Inverted
2-Input NAND Gate with One Input Inverted



Configuration 5 2-Input NOR Gate



Configuration 6 Buffer

Function Selection Table							
Logic Function	Configuration						
2-to-1 Data Selector with inverted output	1						
2-input NAND gate	2						
2-input AND with inverted input	3						
2-input NOR with inverted input	3						
2-input NAND with one inverted input	4						
2-input OR with one inverted input	4						
2-input NOR	5						
1-input Buffer	6						



Absolute Maximum Ratings (Note 4)

Symbol	Description	Rating	Unit
ESD HBM	Human Body Model ESD Protection	2	KV
ESD MM	Machine Model ESD Protection	200	V
V _{CC}	Supply Voltage Range	-0.5 to +6.5	V
VI	Input Voltage Range	-0.5 to +6.5	V
Vo	Voltage applied to output in high impedance or IOFF state	-0.5 to +6.5	V
Vo	Voltage applied to output in high or low state	-0.3 to V _{CC} +0.5	V
I _{IK}	Input Clamp Current V _I <0	-50	mA
lok	Output Clamp Current	-50	mA
lo	Continuous output current	±50	mA
	Continuous current through Vdd or GND	±100	mA
TJ	Operating Junction Temperature	-40 to +150	°C
T _{STG}	Storage Temperature	-65 to +150	°C

Notes:

Recommended Operating Conditions (Note 5)

Symbol		Parameter	Min	Max	Unit
	On and the milder of	Operating	1.65	5.5	V
V _{CC}	Operating Voltage	Data retention only	1.5		V
VI	Input Voltage		0	5.5	V
Vo	Output Voltage		0	V _{CC}	V
		V _{CC} = 1.65V		-4	
	OH High-level output current	V _{CC} = 2.3V		-8	
I _{OH}		ligh-level output current			mA
		$V_{CC} = 3V$		-24	
	V _{CC} = 4.5V			-32	
		V _{CC} = 1.65V		4	
		V _{CC} = 2.3V		8	
I _{OL}	Low-level output current	W 8W		16	mA
		Vcc = 3V		24	
		V _{CC} = 4.5V		32	
		$V_{CC} = 1.8V \pm 0.15V, 2.5V \pm 0.2V$		20	
Δt/ΔV	Input transition rise or fall rate	$V_{CC} = 3.3V \pm 0.3V$		10	ns/V
		V _{CC} = 5 V ± 0.5V		5	
T _A	Operating free-air temperature		-40	+125	°C

Notes: 5. Unused inputs should be held at V_{CC} or Ground.

^{4.} Stresses beyond the absolute maximum may result in immediate failure or reduced reliability. These are stress values and device operation should be within recommend values.



Electrical Characteristics $T_A = -40$ °C to +85°C (All typical values are at $V_{CC} = 3.3$ V, $T_A = +25$ °C)

Symbol	Parameter	Test Conditions	Vcc	Min	Тур.	Max	Unit
			1.65V	0.70		1.20	
	5		2.3V	1.11		1.60	
V_{T+}	Positive-going input threshold voltage		3V	1.50		2.00	
	tilleshold voltage		4.5V	2.16		2.74	
			5.5V	2.61		3.33	
			1.65V	0.30		0.72	
			2.3V	0.58		1.00	
V_{T-}	Negative-going input threshold voltage		3V	0.80		1.30	
	threshold voltage		4.5V	1.21		1.95	
			5.5V	1.45		2.35	
			1.65V	0.30		0.62	
			2.3V	0.40		0.80	
ΔV_T	Hysteresis (V _{T+} - V _{T-)}		3V	0.35		1.00	
			4.5V	0.55		1.10	
			5.5V	0.60		1.20	
		I _{OH} = -100μA	1.65V to 5.5V	V _{CC} - 0.1			
		I _{OH} = -4mA	1.65V	1.2			
		$I_{OH} = -8mA$	2.3V	1.9			.,
V_{OH}	High Level Output Voltage	I _{OH} = -16mA	0)/	2.4			V
		I _{OH} = -24mA	3V	2.3			
		I _{OH} = -32mA	4.5V	3.8			
		I _{OL} = 100μA	1.65V to 5.5V			0.1	
		$I_{OL} = 4mA$	1.65V			0.45	
	18.1.1	I _{OL} = 8mA	2.3V			0.3	.,
V_{OL}	High-level Input Voltage	I _{OL} = 16mA	0)/			0.4	V
		I _{OL} = 24mA	3V			0.55	
		I _{OL} = 32mA	4.5V			0.55	
lı	Input Current	V _I = 5.5V or GND	0 to 5.5V			± 5	μA
I _{OFF}	Power Down Leakage Current	V_I or $V_O = 5.5V$	0			± 10	μA
I _{CC}	Supply Current	V _I = 5.5V of GND I _O = 0	1.65V to 5.5V			10	μΑ
ΔI _{CC}	Additional Supply Current	One input at V _{CC} -0.6V Other inputs at V _{CC} or GND	3V to 5.5V			500	μΑ



Electrical Characteristics $T_A = -40$ °C to +125°C (All typical values are at $V_{CC} = 3.3$ V, $T_A = +25$ °C)

Symbol	Parameter	Test Conditions	V _{CC}	Min	Тур	Max	Unit
			1.65V	0.70		1.20	
			2.3V	1.11		1.60	
V_{T+}	Positive-going input threshold voltage		3V	1.50		2.00	
	tilleshold voltage		4.5V	2.16		2.74	
			5.5V	2.61		3.33	
			1.65V	0.30		0.75	
			2.3V	0.58		1.03	
V_{T-}	Negative-going input threshold voltage		3V	0.80		1.33	
	tilleshold voltage		4.5V	1.21		1.95	
			5.5V	1.45		2.35	
			1.65V	0.30		0.62	
	Hysteresis (V _{T+} - V _{T-)}		2.3V	0.37		0.80	
ΔV_{T}			3V	0.32		1.00	
	(VT+ - VT-)		4.5V	0.50		1.20	
			5.5V	0.55		1.40	
		I _{OH} = -100μA	1.65V to 5.5V	V _{CC} - 0.1			
		I _{OH} = -4mA	1.65V	0.95			
		I _{OH} = -8mA	2.3V	1.7			.,
Vон	High Level Output Voltage	I _{OH} = -16mA		1.9			V
		I _{OH} = -24mA	3V	2.0			
		I _{OH} = -32mA	4.5V	3.4			
		I _{OL} = 100μA	1.65V to 5.5V			0.1	
		I _{OL} = 4mA	1.65V			0.7	
		I _{OL} = 8mA	2.3V			0.45	
V_{OL}	High-level Input Voltage	I _{OL} = 16mA				0.6	V
		I _{OL} = 24mA	3V			0.8	
		I _{OL} = 32mA	4.5V			0.8	
lı	Input Current	V _I = 5.5V or GND	0 to 5.5V			± 100	μA
loff	Power Down Leakage Current	$V_1 \text{ or } V_0 = 5.5V$	0			± 200	μA
I _{CC}	Supply Current	V _I = 5.5V of GND I _O =0	1.65V to 5.5V			200	μА
Δl _{CC}	Additional Supply Current	One input at V _{CC} -0.6V Other inputs at V _{CC} or GND	3V to 5.5V			5000	μΑ



Electrical Characteristics (All typical values are at $V_{CC} = 3.3V$, $T_A = +25$ °C)

Symbol	Parameter	Test Conditions	V _{CC}	Min	Тур	Max	Unit	
C _I	Input Capacitance	$V_I = V_{CC} - or GND$	3.3		3.5		pF	
		SOT26			204			
	Thermal Resistance Junction-to-Ambient	SOT363	(Note 6)		371		0000	
θJA		X2-DFN1410-6			430		°C/W	
		X2-DFN1010-6			510			
		SOT26			52			
	Thermal Resistance Junction-	SOT363	(Note 6)		143		°C/W	
θιс	to-Case	X2-DFN1410-6			190			
		X2-DFN1010-6			250			

Notes:

Switching Characteristics

 $T_A = -40$ °C to +85°C, $C_L = 30$ or 50pF as noted (see Figure 1)

Parameter	From	TO (OUTPUT)	V _{CC} = 1.8V ± 0.15V				V _{CC} = 3.3V ± 0.3V		V _{CC} = 5V ± 0.5V		Unit
	(Input)	(OUTPUT)	Min	Max	Min	Max	Min	Max	Min	Max	
t _{pd}	Any	Υ	1.0	14.4	0.7	8.3	0.7	6.3	0.7	5.1	ns

 $T_A = -40$ °C to +125°C, $C_L = 30$ or 50pF as noted (see Figure 1)

Parameter	From	TO (OUTPUT)	V _{CC} = ± 0.	: 1.8V .15V		: 2.5V).2V		: 3.3V).3V	~ ~	= 5V).5V	Unit
	(Input)	(OUTPUT)	Min	Max	Min	Max	Min	Max	Min	Max	
t _{pd}	Any	Υ	1.0	18.0	0.7	10.4	0.7	7.9	0.7	6.4	ns

Operating Characteristics

 $T_A = +25^{\circ}C$


	Parameter	Test Conditions	V _{CC} = 1.8V	V _{CC} = 2.5V	V _{CC} = 3.3V	V _{CC} = 5V	Unit
$C_{\sf pd}$	Power dissipation capacitance	f = 10 MHz	22	22	23	24	pF

^{6.} Test condition for SOT26, SOT363, X2-DFN1410-6 and X2-DFN1010-6: Device mounted on FR-4 substrate PC board, 2oz copper, with minimum recommended pad layout.



Propagation Delay Times
Inverting and Non Inverting Outputs

Parameter Measurement Information



V	Inputs		•	n	
V _{CC}	VI	t _r /t _f	V _M	CL	RL
1.8V±0.15V	V _{CC}	≤2ns	V _{CC} /2	30pF	1ΚΩ
2.5V±0.2V	Vcc	≤2ns	V _{CC} /2	30pF	500Ω
3.3V±0.3V	3V	≤2.5ns	1.5V	50pF	500Ω
5V±0.5V	V _{CC}	≤2.5ns	V _{CC} /2	50pF	500Ω




Figure 1. Load Circuit and Voltage Waveforms

Notes: A. Includes test lead and test apparatus capacitance.

- B. All pulses are supplied at pulse repetition rate ≤ 10 MHz
- C. Inputs are measured separately one transition per measurement
- D. t_{PLH} and t_{PHL} are the same as t_{PD}

7: Tape & Reel



CONFIGURABLE MULTIPLE-FUNCTION GATE

Ordering Information

74LVC1G 98 XXX - 7

Logic Device Function Package Packing

74 : Logic Prefix 98 : 3-Input W6 : SOT26 LVC : 1.65 to 5.5V Configurable DW : SOT363

Family Multiple-Function FW4: X2-DFN1010-6 1G: One gate Gate FZ4: X2-DFN1410-6


	Double	Packaging Packaging	Packaging	7" Tape and Reel	
	Device	Package Code	(Note 7)	Quantity	Part Number Suffix
Pb	74LVC1G98W6-7	W6	SOT26	3000/Tape & Reel	-7
Pb	74LVC1G98DW-7	DW	SOT363	3000/Tape & Reel	-7
PD	74LVC1G98FW4-7	FW4	X2-DFN1010-6	5000/Tape & Reel	-7
PD,	74LVC1G98FZ4-7	FZ4	X2-DFN1410-6	5000/Tape & Reel	-7

Notes: 7. Pad layout as shown on Diodes Inc. suggested pad layout document AP02001, which can be found on our website at http://www.diodes.com/datasheets/ap02001.pdf.



Marking Information

(1) SOT26, SOT363



XX: Identification code

Y: Year 0~9

W: Week: A~Z: 1~26 week;

a~z: 27~52 week; z represents

52 and 53 week X: A~Z: Internal Code

Part Number	Package	Identification Code
74LVC1G98W6	SOT26	TZ
7/L\/C1G09D\\/	SOTARS	T7

(2) X2-DFN1010-6, X2-DFN1410-6

(Top View)



XX: Identification Code

Y : Year : 0~9

W: Week: A~Z: 1~26 week; a~z: 27~52 week; z represents


52 and 53 week X: A~Z: Internal code

Part Number	Package	Identification Code
74LVC1G98FW4	X2-DFN1010-6	TZ
74LVC1G98Z4	X2-DFN1410-6	TZ




Package Outline Dimensions (All Dimensions in mm)

(1) SOT26



SOT26				
Dim	Min	Max	Тур	
Α	0.35	0.50	0.38	
В	1.50	1.70	1.60	
C	2.70	3.00	2.80	
D	_		0.95	
Н	2.90	3.10	3.00	
7	0.013	0.10	0.05	
K	1.00	1.30	1.10	
L	0.35	0.55	0.40	
M	0.10	0.20	0.15	
α	0°	8°	_	
All Dimensions in mm				

(2) SOT363





SOT363				
Dim	Min	Max		
Α	0.10	0.30		
В	1.15	1.35		
С	2.00	2.20		
D	0.65	Тур		
F	0.40	0.45		
Н	1.80	2.20		
J	0	0.10		
K	0.90	1.00		
L	0.25	0.40		
М	0.10	0.22		
α	0°	8°		
All Dimensions in mm				



Package Outline Dimensions (All Dimensions in mm)


(3) X2-DFN1010-6





X2-DFN1010-6				
Dim	Min	Max	Тур	
Α	_	0.40	0.39	
A 1	0.00	0.05	0.02	
А3	_		0.13	
b	0.14	0.20	0.17	
b1	0.05	0.15	0.10	
D	0.95	1.05	1.00	
Е	0.95	1.05	1.00	
е	_	_	0.35	
L	0.35	0.45	0.40	
K	0.15	_	_	
Z	_	_	0.065	
All Dimensions in mm				

(4) X2-DFN1410-6




X2-DFN1410-6				
Dim	Min	Max	Тур	
Α		0.40	0.39	
A 1	0.00	0.05	0.02	
А3		_	0.13	
b	0.15	0.25	0.20	
D	1.35	1.45	1.40	
Е	0.95	1.05	1.00	
е		_	0.50	
L	0.25	0.35	0.30	
Z		_	0.10	
Z 1	0.045	0.105	0.075	
All Dimensions in mm				




Suggest Pad Layout

(1) SOT26




Dimensions	Value (in mm)
Z	3.20
G	1.60
Х	0.55
Y	0.80
C1	2.40
C2	0.95

(2) SOT363



Dimensions	Value (in mm)
Z	2.5
G	1.3
Х	0.42
Y	0.6
C1	1.9
C2	0.65

(3) X2-DFN1010-6




Dimensions	Value (in mm)
С	0.350
G	0.150
Х	0.200
X1	0.900
Y	0.550
V1	1 250



Suggest Pad Layout

(4) X2-DFN1410-6



Dimensions	Value (in mm)
С	0.500
G	0.250
Х	0.250
X1	1.250
Υ	0.525
Y1	1.250



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel

Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2012, Diodes Incorporated

www.diodes.com