

2A SURFACE-MOUNT FAST RECOVERY BRIDGE RECTIFIER

Product Summary

VRRM (V)	I _F (A)	V _F Max (V)	I _R Max (μA)	
1000	2	1.3	5	

Mechanical Data

- Package: SOPA-4
- Package Material: Plastic Material, UL Flammability Classification 94V-0 (No Br. Sb, Cl)
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 @3
- Polarity Indicator: Symbol Molded on Body
- Weight: 0.93 grams (Approximate)

Features


- Glass Passivated Die Construction
- Rating to 1000V PRV
- Ideal for SMT Manufacturing
- Reliable Low Cost Construction Utilizing Molded Plastic Technique
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please contact us or your local Diodes representative.

https://www.diodes.com/quality/product-definitions/


SOPA-4 (Type WX)







Pin Diagram



Internal Schematic


Ordering Information (Note 4)

Part Number	Paakaga	Packing		
Fait Number	Package	Qty.	Carrier	
ABS20T1M	SOPA-4 (Type WX)	3000	Tape & Reel	

Notes:

- 1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information



ABS20T1M = Product Type Marking Code

Older Marking State Code Marking

YWW = Date Code Marking

Y = Last Digit of Year (ex: 4 = 2024)

WW = Week Code (01 to 53)



Maximum Ratings (@ $T_A = +25$ °C, unless otherwise specified.)

Characteristic			Symbol	Value	Unit
Maximum Repetitive Peak Reverse Voltage			Vrrm	1000	V
Maximum DC Blocking Voltage			V _D C	1000	V
Maximum Average Rectified Output Current	With Heatsink $T_C = +130^{\circ}C$ Without Heatsink $T_C = +120^{\circ}C$		I _{F(AV)}	2 1	Α
Peak Forward Surge Current 8.3ms Single Half Sine Wave T _J = +25°C Superimposed on Rated Load. T _J = +125°C				60 48	Α
		T _J = +25°C T _J = +125°C	IFSM	120 96	Α
I^2 t Rating for Fusing (t = 8.3ms)			l ² t	14.9	A ² s
Operating and Storage Temperature Range			TJ, TSTG	-55 to +150	°C

Electrical Characteristics

Characteristic	Test Conditions		Symbol	Тур	Max	Unit
Forward Voltage	I _F = 2A	$T_J = +25^{\circ}C$	VF	_	1.3	V
Leakage Current	V _R = 1000V	T _J = +25°C T _J = +125°C	IR	_	5 500	μΑ
Reverse Recovery Time	$I_F = 0.5A$, $I_{rr} = 0.25A$, $I_R = 1.0A$		t _{rr}		500	ns
Typical Total Junction Capacitance (Note 5)		Ст	27		pF	

Thermal Characteristics


Characteristic	Symbol	Тур	Unit
Typical Thermal Resistance (Note 6)	Rejc Rejl Reja	6 15 40	°C/W


Notes:

^{5.} Measured at 1.0MHz and applied reverse voltage of 4.0V DC.

^{6.} Thermal resistance junction to case, lead and ambient. Unit mounted on glass-epoxy substrate with 2oz/ft²_30mm x 30mm copper pad.










Figure 2. Maximum Non-Repetitive Surge Current





Figure 4. Typcial Junction Capacitance






Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOPA-4 (Type WX)




	SOPA-4 (Type WX)				
Dim	Min	Max	Тур		
Α	1.20	1.40			
A1	0.00	0.15			
A2	1.20	1.30			
A3	0.43	0.63			
b	0.50	0.80			
С	0.10	0.30			
D	4.85	5.25			
D4	0.45	0.85			
е	3.80	4.20			
Е	6.40	6.80			
E1	4.25	4.65			
E3	5.20	5.60			
E4	0.45	0.85			
L	0.40	0.80			
Ø			7°		
Ø1			7°		
All Dimensions in mm					

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOPA-4 (Type WX)



Dimensions	Value (in mm)	
С	4.00	
X	1.20	
Y	1.80	
Y1	7.20	

March 2024



IMPORTANT NOTICE

- DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functionalsafety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademarks applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
- This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-andconditions/important-notice

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners. © 2024 Diodes Incorporated. All Rights Reserved.

www.diodes.com

ABS20T1M © 2024 Copyright Diodes Incorporated. All Rights Reserved. www.diodes.com Document number: DS44740 Rev. 3 - 2