



AS2376

# LOW-NOISE, LOW QUIESCENT CURRENT, PRECISION OPERATIONAL AMPLIFIER

### **Description**

The AS2376 is a low noise (9.5nV/ $\sqrt{\rm Hz}$ ), low offset (25µV, maximum), operational amplifier that is precision optimized using post-package trim. With a 5.5MHz bandwidth, the device is suitable for a wide array of filtering and control applications.

The low operating voltage range, low quiescent current of  $950\mu A$  (maximum), and excellent PSRR allow for noise-sensitive applications which are supplied from noisy low-voltage rails.

The dual AS2376 is offered in the SO-8 and MSOP-8 package, specified for operation from -40 $^{\circ}$ C to +125 $^{\circ}$ C.

#### **Features**

Low Noise: 9.5nV/√Hz at 1kHz
 0.1Hz to 10Hz Noise: 0.8µV<sub>PP</sub>

Quiescent Current: 760µA (typical)

Low Offset Voltage: 5µV (typ)

• Gain Bandwidth Product: 5.5MHz

· Rail-to-Rail Input and Output

Single-Supply Operation


Supply Voltage: 2.2V to 5.5V


Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)

Halogen and Antimony Free. "Green" Device (Note 3)

 An automotive-compliant part is available under separate datasheet (AS2376Q)

### **Pin Assignments**





### **Applications**


- Auto pumps
- Position sensors
- Vehicle occupant detection sensors
- Airbags
- Onboard charges (OBC)
- DC-DC converters
- Battery management systems (BMS)

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.



# **Typical Applications Circuit**




**Basic Single Power Amplifier Connection** 

# **Pin Description**

PIN		1/0	DESCRIPTION
NAME	SO-8/MSOP-8	1/0	DESCRIPTION
+IN A	3	I	Noninverting input, channel A
+IN B	5	I	Noninverting input, channel B
–IN A	2	I	Inverting input, channel A
–IN B	6	I	Inverting input, channel B
OUT A	1	0	Output, channel A
OUT B	7	0	Output, channel B
V+	8	_	Positive (highest) power supply
V-	4	_	Negative (lowest) power supply

# **Functional Block Diagram**



**AS2376 Functional Block** 



# Absolute Maximum Ratings (Note 4) (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Symbol	Parameter	Rati	Rating		
V+ -V-	Supply Voltage	6.5	5	V	
-	Output Short Circuit to V+	(Note	e 5)	-	
-	Output Short Circuit to V-	(Note	e 6)	-	
Commont.	Signal input terminals (Note 7)	(Note	e 7)	mA	
Current	Output short-circuit (Note 8)	Contin	uous	mA	
T <sub>ST</sub>	Storage Temperature	-65 to	-65 to +150		
TJ	Maximum Junction Temperature	+15	+150		
$T_{LEAD}$	Lead Temperature (Soldering, 10 Seconds)	+26	+260		
D	lunction to Ambient Thermal Decistors	SO-8	115	***************************************	
$R_{\theta JA}$	Junction-to-Ambient Thermal Resistance	MSOP-8	210	°C/W	
1		SO-8	18	9000	
R <sub>eJC</sub>	Junction-to-Case Thermal Resistance	MSOP-8	40	°C/W	
ESD HBM	Human Body Model ESD Protection	4	4		
ESD CDM	Charged-device Model ESD Protection	1	·	kV	

Notes:

- 4. Absolute Maximum Ratings indicate limits beyond which damage to the device may occur. Operating Ratings indicate conditions for which the device is intended to be functional, but specific performance is not guaranteed. For guaranteed specifications and the test conditions, see the
- Electrical Characteristics.

  5. Shorting output to V+ will adversely affect reliability.

  6. Shorting output to V- will adversely affect reliability.
- 7. Input terminals are diode-clamped to the power-supply rails. Input signals that can swing more than 0.3V beyond the supply rails should be current limited to 10mA or less.
- 8. Short-circuit to ground.

# **Recommended Operating Conditions**

Symbol	Parameter	Min.	Max.	Unit
V <sub>CC</sub>	Supply Voltage	2.2	5.5	V
T <sub>A</sub>	Ambient Operating Temperature Range	-40	+125	°C



**Electrical Characteristics** (Limits in standard typeface are for  $T_A$  = +25°C, **bold** typeface applies over -40°C to +125°C (Note 9),  $R_L$  = 10 kΩ connected to  $V_S$  / 2,  $V_{CM}$  =  $V_S$  / 2, and  $V_{OUT}$  =  $V_S$  / 2, unless otherwise noted.)

SYMBOL	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
OFFSET \						•
		-	-	5	25	μV
Vos	Input offset voltage (Note 10)	Long-term stability (Note 11)	-	_	60	μV
		Package level shift (Note 12)	-	-	320	μV
		T <sub>A</sub> = -40°C to +85°C	-	0.26	1.2	μV/°C
ΔV <sub>OS</sub> /ΔT	Input offset voltage versus temperature	T <sub>A</sub> = -40°C to +125°C	-	0.32	2	μV/°C
	tomporature	$T_A = 25^{\circ}C$ , $V_S = 2.2V$ to 5.5V, $V_{CM} < (V^{+}) - 1.3V$	-	5	20	μV/V
PSRR	Input offset voltage versus power supply	$T_A = -40$ °C to +125°C,	-	5	-	μV/V
		$V_S = 2.2V \text{ to } 5.5V, V_{CM} < (V^+) - 1.3V$				
-	Channel separation, dc		-	0.5	-	mV/V
INPUT BIA	AS CURRENT	T 0500	<u> </u>	0.0	70	A
I <sub>B</sub>	Input bias current	T <sub>A</sub> = 25°C	-	0.2	70	pA
'B		$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$	See Typ	oical Chara	cteristics	pA
IOS	Input offset current	-	-	0.2	70	pA
NOISE						
-	Input voltage noise	f = 0.1Hz to 10Hz	-	8.0	-	$\mu V_{PP}$
e <sub>n</sub>	Input voltage noise density	f = 1kHz	-	9.5	-	nV/ <mark>√Hz</mark>
In	Input current noise	f = 1kHz	-	2	-	fA/√Hz
INPUT VO	LTAGE RANGE		•		•	•
V <sub>CM</sub>	Common-mode voltage range	-	(V <sup>-</sup> ) − 0.1	-	(V <sup>+</sup> ) + 0.1	V
CMRR	Common-mode rejection ratio	$(V^-) < V_{CM} < (V^+) - 1.3 \text{ V}$	76	90	-	dB
-	Differential	-	-	6.5	-	pF
-	Common-mode	-	-	13	-	pF
OPEN-LO	OP GAIN		ı		1	
		$50\text{mV} < V_O < (V^+) - 50\text{mV}, R_L = 10\text{k}\Omega$	120	134	-	dB
A <sub>OL</sub>	Open-loop voltage gain	$100 \text{mV} < \text{V}_{\text{O}} < (\text{V}^{+}) - 100 \text{mV}, R_{\text{L}} = 2 \text{k}\Omega$	120	126	-	dB
FREQUEN	ICY RESPONSE C <sub>L</sub> = 100 pF, \	/ <sub>S</sub> = 5.5 V			_	T
GBW	Gain-bandwidth product	-	-	5.5	-	MHz
SR	Slew rate	G = 1	-	2	-	V/µs
		Settling to 0.1%, 2-V step , G = 1	-	1.6	-	μs
t <sub>S</sub>	Settling time	Settling to 0.01%, 2-V step , G = 1	-	2	-	μs
-	Overload recovery time	$V_{IN} \times gain > V_{S}$	-	0.33	-	μs
-	Overload recovery time	$V_{IN} \times gain > V_{S}$	-	0.33	-	μs
		5				

Notes:

<sup>9.</sup> Limits over the full temperature are guaranteed by design, but not tested in production.
10. After mounted to PCB, Vos value will be different to spec, the delta value depend on PCB solder stress, the max value is between +/- 80µV, per our

<sup>11.</sup> AS2376Q, the long-term stability is defined as MAX. Vos shift during life HTOL 1000 hours with TA=+125°C (Tj=150°C). This Vos drift with time is not a linear function of time, and the shift is greater initially and diminishes over time. This parameter is guaranteed by design. 12. After HTSL 2000 hours with TA=+150°C, the Vos drift test condition is TA=+125°C.




**Electrical Characteristics** (continued) (Limits in standard typeface are for  $T_A$  = +25°C, **bold** typeface applies over -40°C to +125°C (Note 9),  $R_L$  = 10kΩ connected to  $V_S$  / 2,  $V_{CM}$  =  $V_S$  / 2, and  $V_{OUT}$  =  $V_S$  / 2, unless otherwise noted.)

SYMBOL	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT	
OUTPUT	OUTPUT						
		$T_A = 25^{\circ}C$ , $R_L = 10k\Omega$	-	10	20	mV	
-	Voltage output swing from rail	$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}, R_L = 10\text{k}\Omega$	-	-	40	mV	
	Trom ruii	$T_A = 25^{\circ}C$ , $R_L = 2k\Omega$	-	40	50	mV	
		$T_A = -40$ °C to +125°C, $R_L = 2k\Omega$	-	-	80	mV	
I <sub>SC</sub>	Short-circuit current	-		+30, -50		mA	
$C_{LOAD}$	Capacitive load drive	-	See Ty	ypical Characte	ristics	-	
Ro	Open-loop output	-	-	150	-	Ω	
POWER S	UPPLY						
	Specified voltage range	-	2.2	-	5.5	V	
Vs	Operating voltage range	-	-	2 to 5.5	-	V	
Io	Quiescent current per	$T_A = 25^{\circ}C$ , $I = 0$ , $V = 5.5$ V, $VCM < (V^+) - 1.3$ V	-	760	950	μΑ	
IQ	amplifier	T <sub>A</sub> = -40°C to +125°C	-	-	1	mA	
TEMPER A	TEMPERATURE						
-	Specified range	-	-40	-	+125	°C	
-	Operating range	-	-40	-	+150	°C	

Note: 9. Limits over the full temperature are guaranteed by design, but not tested in production.





### **Performance Characteristics**








### **Performance Characteristics** (continued)


















### **Performance Characteristics** (continued)






### **Performance Characteristics** (continued)


#### **Positive Output Overload Recovery**




#### **Negative Output Overload Recovery**




#### **Positive Output Overload Recovery**




### **Negative Output Overload Recovery**



#### 0.1-Hz to 10-Hz Input Voltage Noise



0.1-Hz to 10-Hz Input Voltage Noise






### **Application Information**

#### Overview

The AS2376 combines low offset (25µV maximum) and 5.5-MHz bandwidth for a wide variety of filtering and control applications. Many op amps use chopper stabilization to achieve low offset voltage, but this normally comes with a restriction of bandwidth to less than 500kHz. The offset of the AS2376 is addressed by using post-package trim, allowing for the retention of significant bandwidth.

#### Stability considerations when driving capacitive loads


Operational amplifiers are prone to oscillation when required to drive large capacitive loads. The AS2376 is capable of driving a 250 picofarad load at unity gain. Larger loads will require the insertion of a nulling resistor (denoted as  $R_s$ ) in series with the load capacitor. The suggested nulling resistor value is  $10\Omega$  to  $20\Omega$ . This addition will introduce a small error but is negligible in most applications.



Circuit for Driving Large Capacitive Loads

#### Offset voltage as input common mode approaches V+


The AS236 has an input circuitry configuration that is common to most rail-to-rail input operational amplifiers. At the low end of the common mode input voltage range, the input signals are processed by a differential pair of PMOS transistors. This portion of the circuit is precision adjusted with post package trim allowing the offset to be in the microvolts range. As the input common mode voltage approaches approximately one volt less than the positive supply, the inputs are transitioned to a second differential pair of NMOS transistors. This portion of the op amp has an offset voltage similar to a conventional op amp. As noted in the heading of the Electrical Characteristics section, the precision offset voltage is optimized at a common mode of one half of the supply voltage. This conceptual chart depicts the approximate best case of extending the precision common mode area by using the device at 5.5V supply.



Offset Voltage over Common Mode Voltage Range



# **Ordering Information** (Note 10)




Orderable Part Number	Package Code Package		Packing		
Orderable Part Number	Package Code	Fackage	Quantity	Carrier	Part Number Suffix
AS2376S-13	S	SO-8	2,500	Tape and Reel	-13
AS2376M8-13	M8	MSOP-8	2,500	Tape and Reel	-13

Note: 10. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

# **Marking Information**

#### (1) SO-8




YY: Year: 19, 20, 21~ WW : Week : 01~52; 52 represents 52 and 53 week

XX: Internal Code

Orderable Part Number	Package	Identification Code
AS2376S-13	SO-8	AS2376

### (2) MSOP-8




Orderable Part Number	Package	Identification Code
AS2376M8-13	MSOP-8	AS2376




# **Package Outline Dimensions**

Please see http://www.diodes.com/package-outlines.html for the latest version.




SO-8						
Dim	Min	Max	Тур			
Α	1.40	1.50	1.45			
A1	0.10	0.20	0.15			
b	0.30	0.50	0.40			
С	0.15	0.25	0.20			
D	4.85	4.95	4.90			
E	5.90	6.10	6.00			
E1	3.80	3.90	3.85			
E0	3.85	3.95	3.90			
е			1.27			
h	-		0.35			
L	0.62	0.82	0.72			
Q	0.60	0.70	0.65			
All	Dimens	ions in	mm			



**SO-8** 

MSOP-8




MSOP-8						
Dim	Min	Max	Тур			
Α		1.10				
A1	0.05	0.15	0.10			
A2	0.75	0.95	0.86			
А3	0.29	0.49	0.39			
b	0.22	0.38	0.30			
С	0.08	0.23	0.15			
D	2.90	3.00				
Е	4.70	5.10	4.90			
E1	2.90	3.10	3.00			
E3	2.85	3.05	2.95			
е			0.65			
L	0.40	0.80	0.60			
а	0°	8°	4°			
Х			0.750			
у			0.750			
aaa	0.20					
bbb	0.25					
ССС	0.10					
ddd		0.13				
All Dimensions in mm						

See Detail C




# **Suggested Pad Layout**

Please see http://www.diodes.com/package-outlines.html for the latest version.



<b>Dimensions</b>	Value (in mm)
С	1.27
Х	0.802
X1	4.612
Y	1.505
Y1	6.50

#### MSOP-8



Dimensions	Value (in mm)
С	0.650
Х	0.450
Υ	1.350
Y1	5.300

### **Mechanical Data**

#### **SO-8**

- Package Material: Molded Plastic, UL Flammability Rating 94V-0
- Terminals: Finish Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 @3
- Weight: 0.074 grams (Approximate)
- Max Soldering Temperature +260°C for 30 secs as per JEDEC J-STD-020

#### MSOP-8

- Package Material: Molded Plastic, UL Flammability Rating 94V-0
- Terminals: Finish Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 @3
- Weight: 0.035 grams (Approximate)
- Max Soldering Temperature +260°C for 30 secs as per JEDEC J-STD-020



#### IMPORTANT NOTICE

- DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and
- Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- provided subject Diodes' Standard (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
- 9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-andconditions/important-notice

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners. © 2023 Diodes Incorporated. All Rights Reserved.

www.diodes.com

14 of 14 AS2376 May 2023 © 2023 Copyright Diodes Incorporated. All Rights Reserved. www.diodes.com