

ASMA6J SERIES

SURFACE MOUNT UNIDIRECTIONAL AND BIDIRECTIONAL TRANSIENT VOLTAGE SUPPRESSORS

STAND-OFF VOLTAGE - 5.0 to 75 Volts
POWER DISSIPATION -600 Watts

FEATURES




- For surface mounted applications
- Reliable low cost construction utilizing molded plastic technique
- Typical IR less than 1uA above 10V
- Fast response time: typically less than 1.0ns for Uni-direction, less than 5.0ns for Bi-direction, from 0 Volts to BV min
- AEC-Q101 qualified
- PPAP capable
- **Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)**
- **Halogen and Antimony Free. "Green" Device (Note 3)**

MECHANICAL DATA

- Package: Molded plastic
- Package Material: Molding compound, UL Flammability classification 94V-0, (No Br. Sb. Cl.) "Halogen-free".
- Polarity: by cathode band denotes uni-directional device none cathode band denotes bi-directional device
- Moisture Sensitivity: Max Soldering Temperature +260°C for 30 secs as per JEDECJ-STD-020
- Terminals Finish: Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208
- Weight: 0.064 grams (Approximate)

SMA



SMA		
DIM.	MIN.	MAX.
A	4.06	4.57
B	2.29	2.92
C	1.27	1.63
D	0.15	0.31
E	4.83	5.59
F	0.05	0.20
G	1.96	2.40
H	0.76	1.52
All Dimensions in millimeter		

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.

ABSOLUTE RATINGS

PARAMETER	SYMBOL	VALUE	UNIT
Peak pulse power at T _j =25°C, T _p =1ms (Note 4)	P _{PK}	600	W
Peak Forward Surge Current 8.3ms single half sine-wave@T _j =25°C (Note 5)	I _{FSM}	60	A
Steady State Power Dissipation with PCB	P _{M(AV)}	1.5	W
Maximum Instantaneous forward voltage at 16A (Notes 5, 6)	V _F	SEE NOTE 6	V
Typical Thermal Resistance (Note 7)	R _{thJA}	75	°C/W
	R _{thJL}	25	
	R _{thJC}	15	
Operating Temperature Range	T _J	-55 to +175	°C
Storage Temperature Range	T _{STG}	-55 to +175	°C

Notes:







1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
2. See <https://www.diodes.com/quality/lead-free/> for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
4. Non-repetitive current pulse, per fig. 3 and derated above T_J= 25°C per fig.1.
5. Only for unidirectional units.
6. V_F max=2.5V at I_F=16 A 300us square wave pulse.
7. Thermal resistance from junction to ambient, lead and case.

ELECTRICAL CHARACTERISTICS

Device Uni- Directional	Device Bi- Directional	Device Marking Code		Reverse Standoff Voltage	Breakdown Voltage VBR Volts			Max. Clamping Voltage @Ipp	Max. Peak Pulse Current	Max. Reverse Leakage @ VR
		(UNI)	(BI)		Min.	Max.	@It (mA)			
ASMA6J5.0A		AOE		5.0	6.40	7.07	10	9.1	68.0	100.0
ASMA6J6.0A		AOG		6.0	6.70	7.41	10	9.5	61	100.0
ASMA6J6.5A		AOK		6.5	7.20	7.96	10	11.2	53.6	100.0
ASMA6J7.0A		AOM		7.0	7.78	8.60	10	12.0	50.0	20.0
ASMA6J7.5A		AOP		7.5	8.33	9.21	1.0	12.9	46.5	20.0
ASMA6J8.0A		AOR		8.0	8.89	9.83	1.0	13.6	44.1	20.0
ASMA6J8.5A		AOT		8.5	9.4	10.4	1.0	13.3	41.7	20.0
ASMA6J9.0A		AOV		9.0	10.0	11.1	1.0	15.4	39.0	20.0
ASMA6J10A	ASMA6J10CA	ASX	AJX	10.0	11.1	12.3	1.0	15.7	37	0.2
ASMA6J11A	ASMA6J11CA	ASZ	AJZ	11.0	12.2	13.5	1.0	18.2	33.0	0.2
ASMA6J12A	ASMA6J12CA	ASE	AJE	12.0	13.3	14.7	1.0	18.8	31.0	0.2
ASMA6J13A	ASMA6J13CA	ASG	AJG	13.0	14.4	15.9	1.0	20.4	29.0	0.2
ASMA6J14A	ASMA6J14CA	ASK	AJK	14.0	15.6	17.2	1.0	23.2	25.8	0.2
ASMA6J15A	ASMA6J15CA	ASM	AJM	15.0	16.7	18.5	1.0	23.6	25.1	0.2
ASMA6J16A	ASMA6J16CA	ASD	AJP	16.0	17.8	19.7	1.0	26.0	23.1	0.2
ASMA6J17A	ASMA6J17CA	ASN	AJR	17.0	18.9	20.9	1.0	27.6	21.7	0.2
ASMA6J18A	ASMA6J18CA	ASK	AJT	18.0	20.0	22.1	1.0	28.3	21.5	0.2
ASMA6J20A	ASMA6J20CA	AQV	AKV	20.0	22.2	24.5	1.0	31.4	19.4	0.2
ASMA6J22A	ASMA6J22CA	AQX	AKX	22.0	24.4	27.0	1.0	35.5	16.9	0.2
ASMA6J24A	ASMA6J24CA	AQZ	AKZ	24.0	26.7	29.5	1.0	37.8	16.0	0.2
ASMA6J26A	ASMA6J26CA	AQE	AKE	26.0	28.9	31.9	1.0	40.9	14.9	0.2
ASMA6J28A	ASMA6J28CA	AQG	AKG	28.0	31.1	34.4	1.0	44.0	13.8	0.2
ASMA6J30A	ASMA6J30CA	AQK	AKK	30.0	33.3	36.8	1.0	48.4	12.4	0.2
ASMA6J33A	ASMA6J33CA	AQM	AKM	33.0	36.7	40.6	1.0	51.9	11.8	0.2
ASMA6J36A	ASMA6J36CA	AQP	AKP	36.0	40.0	44.2	1.0	58.1	10.3	0.2
ASMA6J40A	ASMA6J40CA	ASR	ANR	40.0	44.4	49.1	1.0	62.8	9.7	0.2
ASMA6J43A	ASMA6J43CA	AST	ANT	43.0	47.8	52.8	1.0	69.4	8.6	0.2
ASMA6J45A	ASMA6J45CA	ASV	ANV	45.0	50.0	55.3	1.0	72.7	8.3	0.2
ASMA6J48A	ASMA6J48CA	ASX	ANX	48.0	53.3	58.9	1.0	75.4	8.1	0.2
ASMA6J51A	ASMA6J51CA	AFZ	ANZ	51.0	56.7	62.7	1.0	82.4	7.3	0.2
ASMA6J54A	ASMA6J54CA	AFC	ANE	54.0	60.0	66.3	1.0	87.1	6.9	0.2
ASMA6J58A	ASMA6J58CA	ASG	ALG	58.0	64.4	71.2	1.0	91.1	6.7	0.2
ASMA6J60A	ASMA6J60CA	ASK	ALK	60.0	66.7	73.7	1.0	96.8	6.2	0.2
ASMA6J64A	ASMA6J64CA	ASM	ALM	64.0	71.1	78.6	1.0	103	5.8	0.2
ASMA6J70A	ASMA6J70CA	ASP	ALP	70.0	77.8	86.0	1.0	110	5.5	0.2
ASMA6J75A	ASMA6J75CA	ASR	ALR	75.0	83.3	92.1	1.0	121	4.9	0.2

Notes:


- 1) Suffix 'A ' denotes 5% tolerance device, no suffix denotes 10 % tolerance device.
- 2) Add suffix 'C 'or ' CA ' after part number to specify Bi-directional devices.
- 3) The IR limit is double for Bi-Directional devices.
- 4) Only Uni-directional type of 10 V and less.

**RATING AND CHARACTERISTIC CURVES
 ASMA6J SERIES**


Ordering Information :

Part Number	Package	Packing	
		Qty.	Carrier
ASMA6J SERIES	SMA	5000pcs	Reel

Marking Information :




XXXX : Assembly Tracing code
ZZZ : Product Type Marking code
Bar Denotes Cathode Side

Packaging Information :

DEVICE	Q'TY/REEL (PCS)	REEL DIA. (INCH)	Q'TY/BOX (PCS)	Q'TY/CARTON (PCS)
ASMA6JXXA ASMA6JXXCA	5000	13	10K	80K

Suggested Pad Layout :

SMA



Dimensions	Value (in mm)
C	4.00
G	1.50
X	2.50
X1	6.50
Y	1.70

Note: The suggested land pattern dimensions have been provided for reference only, as actual pad layouts may vary depending on application. These dimensions may be modified based on user equipment capability or fabrication criteria. A more robust pattern may be desired for wave soldering and is calculated by adding 0.2 mm to the 'Z' dimension. For further information, please reference document IPC-7351A, Naming Convention for Standard SMT Land Patterns, and for International grid details, please see document IEC, Publication 97.

Note: For high voltage applications, the appropriate industry sector guidelines should be considered with regards to creepage and clearance distances between device Terminals and PCB tracking.

IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (<https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/>) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

9. This Notice may be periodically updated with the most recent version available at <https://www.diodes.com/about/company/terms-and-conditions/important-notice>

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries.
All other trademarks are the property of their respective owners.
© 2023 Diodes Incorporated. All Rights Reserved.

www.diodes.com