

# SINGLE LOW VOLTAGE RAIL-TO-RAIL OUTPUT OPERATIONAL AMPLIFIER

#### **Description**

The AZV321 is single low voltage (2.7V to 5.5V) operational amplifier which has rail-to-rail output swing capability. The input common-mode voltage range includes ground. The chip exhibits excellent speed-power ratio, achieving 1MHz of bandwidth and 1V/µs of slew rate with low supply current.

The AZV321 is built with BiCMOS process. It has bipolar input and output stages for improved noise performance, low input offset and higher output current drive.

The AZV321 is available in the package of SC-70-5, which is approximately half the size of SOT-23-5. The small package saves space on pc boards, and enables the design of small portable electronic devices. It also allows the designer to place the device closer to the signal source to reduce noise pickup and increase signal integrity.

The AZV321 is also available in standard SOT-23-5 package.


**Features** (For  $V_{CC}$ =5V and  $V_{EE}$ =0V, Typical unless Otherwise Noted)

- Guaranteed 2.7V to 5.5V Performance
- No Crossover Distortion
- Gain-Bandwidth Product 1MHz
- Industrial Temperature Range: -40°C to +85°C
- Low Supply Current: 130μA
- Rail-to-Rail Output Swing under  $10k\Omega$  Load:

 $V_{OH}$  up to  $V_{CC}$ -10mV  $V_{OL}$  near to  $V_{EE}$ +65mV  $V_{CM}$ : -0.1V to  $V_{CC}$ -0.8V

## Pin Assignments


KS/K Package (SC-70-5/SOT-23-5)



## **Applications**

- Active Filters
- Low Power, Low Voltage Applications
- General Purpose Portable Devices
- Cellular Phone, Cordless Phone
- Battery-Powered Systems

## **Functional Block Diagram**







**AZV321** 

### Absolute Maximum Ratings (Note 1)

Symbol	Parameter	Rating	Unit
V <sub>CC</sub>	Power Supply Voltage	6	٧
T <sub>J</sub>	Operation Junction Temperature	150	°C
T <sub>STG</sub>	Storage Temperature Range	-65 to 150	°C
T <sub>LEAD</sub>	Lead Temperature (Soldering, 10 Seconds)	260	°C
	ESD (Machine Model)	200	V
	ESD (Human Body Model)	2000	V

Note 1: Stresses greater than those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "Recommended Operating Conditions" is not implied. Exposure to "Absolute Maximum Ratings" for extended periods may affect device reliability.

## **Recommended Operating Conditions**

Symbol	Parameter	Min	Max	Unit
V <sub>CC</sub>	Supply Voltage	2.7	5.5	V
T <sub>A</sub>	Ambient Operating Temperature Range	-40	85	°C





**AZV321** 

### **Electrical Characteristics**

**AZV321-2.7V Electrical Characteristics** (All limits are guaranteed for  $T_A$ =25°C,  $V_{CC}$ =2.7V,  $V_{EE}$ =0V,  $V_{CM}$ =1.0V,  $V_O$ = $V_{CC}$ /2 and  $R_L$ >1M $\Omega$ , limits in **bold types** are guaranteed for  $T_A$ =-40°C to 85°C, unless otherwise specified. Note 2)

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
\/	Input Offset Voltage			1.7	7	m\/
V <sub>IO</sub>	Input Offset Voltage	itage			9	mV
1	January Dina Comment			11	250	^
l <sub>Β</sub>	Input Bias Current				500	nA
1	Input Offset Current			5	50	nA
I <sub>IO</sub>	Input Offset Current				150	IIA
V <sub>CM</sub>	Input Common Mode Voltage Range	for CMRR≥50dB	-0.1		1.9	V
,	Supply Current	V <sub>O</sub> =V <sub>CC</sub> /2, A <sub>VCL</sub> =1, no load		80	170	μΑ
I <sub>CC</sub>					270	
CMRR	Common Mode Rejection Ratio	0≤V <sub>CM</sub> ≤1.7V	50	65		dB
PSRR	Power Supply Rejection Ratio	2.7V≤V <sub>CC</sub> ≤5V, V <sub>O</sub> =1V	50	60		dB
I <sub>SOURCE</sub>	Outside Object Circuit Comment	V <sub>O</sub> =0V	5	20		mA
I <sub>SINK</sub>	Output Short Circuit Current	V <sub>O</sub> =2.7V	10	30		mA
V <sub>OH</sub>	Outrot Valta na Outra	D 401-0 t- 4.051/	2.60	2.69		V
V <sub>OL</sub>	Output Voltage Swing	$R_L$ =10kΩ to 1.35V		60	180	mV
GBWP	Gain Bandwidth Product	C <sub>L</sub> =200pF		1		MHz
фм	Phase Margin			60		Deg
G <sub>M</sub>	Gain Margin			10		dB

Note 2: Limits over the full temperature are guaranteed by design, but not tested in production.




## **Electrical Characteristics** (Cont.)

**AZV321-5V Electrical Characteristics** (All limits are guaranteed for  $T_A$ =25°C,  $V_{CC}$ =5V,  $V_{EE}$ =0V,  $V_{CM}$ =2.0V,  $V_O$ = $V_{CC}$ /2 and  $R_L$ >1M $\Omega$ , limits in **bold types** are guaranteed for  $T_A$ =-40°C to 85°C, unless otherwise specified. Note 2)

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
1/	Innut Official Voltage			1.7	7	
$V_{IO}$	Input Offset Voltage				9	mV
1	Input Ding Current			11	250	η.Λ
l <sub>Β</sub>	Input Bias Current				500	nA
I <sub>IO</sub>	Input Offset Current			5	50	nA
IIO	·				150	ПА
$V_{CM}$	Input Common Mode Voltage Range	for CMRR≥50dB	-0.1		4.2	V
laa	Supply Current	V <sub>O</sub> =V <sub>CC</sub> /2, A <sub>VCL</sub> =1, no load		130	250	^
Icc	Supply Current	V0-VCC/2, AVCL-1, 110 10au			350	μA
Gv	Lorgo Signal Voltago Cain	R <sub>L</sub> =2kΩ	84	100		dB
9	Large Signal Voltage Gain	KL-2K11	80			
CMRR	Common Mode Rejection Ratio	0≤V <sub>CM</sub> ≤4V	50	65		dB
PSRR	Power Supply Rejection Ratio	2.7V≤V <sub>CC</sub> ≤5V, V <sub>O</sub> =1V, V <sub>CM</sub> =1V	50	60		dB
I <sub>SOURCE</sub>	Output Short Circuit Current	V <sub>O</sub> =0V	5	60		mA
I <sub>SINK</sub>	Output Short Circuit Current	V <sub>O</sub> =5V	10	160		mA
		$R_L$ =2k $\Omega$ to 2.5V	4.7	4.96		- V
$V_OH$			4.6			
VOH		R <sub>L</sub> =10kΩ to 2.5V	4.9	4.99		
	Output Voltage Swing	N10K22 (0 2.5V	4.8			
	Output Voltage Owing	$R_L$ =2k $\Omega$ to 2.5V		120	300	
$V_{OL}$		N2N12 to 2.5V			400	mV
VOL		D -40k0 to 2.5V		65	180	1117
		$R_L$ =10k $\Omega$ to 2.5V			280	
SR	Slew Rate			1		V/µS
GBWP	Gain Bandwidth Product	C <sub>L</sub> =200pF		1		MHz
φм	Phase Margin			60		Deg
$G_M$	Gain Margin			10		dB


Note 2: Limits over the full temperature are guaranteed by design, but not tested in production.






### **Performance Characteristics**


#### Supply Current vs. Supply Voltage




#### **Output Source Current vs. Supply Voltage**




### Short Circuit Current $_{I_{SINK}}$ vs. Temperature




#### Slew Rate vs. Supply Voltage



#### **Output Sink Current vs. Supply Voltage**




### Short Circuit Current\_I<sub>SOURCE</sub> vs. Temperature






#### **Performance Characteristics (Cont.)**


#### **Output Voltage vs. Source Current**




#### **Output Voltage Swing vs. Supply Voltage**




Gain and Phase vs. Frequency and Resistive Load




#### **Output Voltage vs. Sink Current**




#### **Output Voltage Swing vs. Temperature**



Gain and Phase vs. Frequency and Capacitive Load









#### **Performance Characteristics (Cont.)**


# Gain and Phase vs. Frequency and Capacitive Load




# Non-Inverting Input Large Signal Pulse Response




#### **Output with Excessive Capacitive Load**




# Non-Inverting Input Small Signal Pulse Response



#### **Output with Excessive Capacitive Load**




THD+N vs. Frequency






## **Ordering Information**



Packers Temperature		Part Number		Marking ID		Dooking Tune	
Package	Range	Lead Free	Green	Lead Free	Green	Packing Type	
SC-70-5		AZV321KSTR-E1	AZV321KSTR-G1	21	B1	Tape & Reel	
SOT-23-5	-40 to 85°C	AZV321KTR-E1	AZV321KTR-G1	E6D	G6D	Tape & Reel	


BCD Semiconductor's Pb-free products, as designated with "E1" suffix in the part number, are RoHS compliant. Products with "G1" suffix are available in green packages.





## Package Outline Dimensions (All dimensions in mm(inch).)


#### SC-70-5





## Package Outline Dimensions (Cont. All dimensions in mm(inch).)


#### SOT-23-5





## Suggested Pad Layout

## SC-70-5




Dimongions	Z	G	X	Y	Е	E1
Dimensions	(mm)/(inch)	(mm)/(inch)	(mm)/(inch)	(mm)/(inch)	(mm)/(inch)	(mm)/(inch)
Value	2.740/0.108	1.140/0.045	0.400/0.016	0.800/0.031	1.300/0.051	0.650/0.026



## Suggested Pad Layout (Cont.)

## SOT-23-5



Dimonsions	Z	G	X	Y	E1	E2
Dimensions	(mm)/(inch)	(mm)/(inch)	(mm)/(inch)	(mm)/(inch)	(mm)/(inch)	(mm)/(inch)
Value	3.600/0.142	1.600/0.063	0.700/0.028	1.000/0.039	0.950/0.037	1.900/0.075



**AZV321** 

#### **IMPORTANT NOTICE**

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

#### **LIFE SUPPORT**

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
  - 1. are intended to implant into the body, or
  - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2013, Diodes Incorporated

www.diodes.com